


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	17NOV2017	TS	EI
	AI	REVISED PER ECR-18-010487	05JUL2018	RI	EI



3.9	4.8	3.09	3.2	25.8	3.1-3.8	3L	AWG16-14 1.25-2.2SQmm	2	AU 0.38umMIN	2316817-5
3.96	3.64	3.09	3.2	25.8	2.2-2.8	2L	AWG16-14 1.25-2.2SQmm	2	AU 0.38umMIN	2316817-4
3.96	3.64	2.9	2.9	25.3	1.8-2.8	L	AWG20-16 0.5-1.42SQmm	2	AU 0.38umMIN	2316817-3
3.64	3.6	2.15	2.3	25.3	1.2-2.6	M	AWG24-20 0.2-0.5SQmm	2	AU 0.38umMIN	2316817-2
2.5	2.6	1.81	1.8	25.3	0.8-1.4	S	AWG28-24 0.08-0.2SQmm	2	AU 0.38umMIN	2316817-1
AE	AD	AC	AB	AA	INSUL. RANGE	SIZE ID	WIRE RANGE	PLATING ID	CONTACT POINT PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
COPPER ALLOY

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±°

1 PLC ±0.4

2 PLC ±0.4

3 PLC ±0.4

4 PLC ±0.4

ANGLES ±5°

FINISH
AU OVER NI

AT CONTACT AREA

DWN
T. SHIMOYASU
17NOV2017

CHK
E. IKEMATSU
17NOV2017

APVD
E. IKEMATSU
17NOV2017

PRODUCT SPEC
108-140158

APPLICATION SPEC
114-78024

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
CONTACT, LOOSE PIECE, TAB, HD3
HDC DYNAMIC

SIZE
A300779

CAGE CODE
C-2316817

DRAWING NO

RESTRICTED TO
-

SCALE
5:1

SHEET
1 OF 1

REV
AI

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2316817-5](#)