

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED	11MAY2019	CJV	JW
B		REVISED PER ECO-19-011736	07AUG2019	AP	JW
C		REVISED PER ECO-20-015351	28OCT2020	TX	DZ

△ HOUSING AND CONTACT OVERMOLDS - LCP, UL94-V0, BLACK.
CONTACTS AND HOLD DOWNS - COPPER ALLOY.
PICK AND PLACE TAPE - POLYIMIDE FILM.

△ CONTACTS - GOLD PLATE ON MATING SURFACES,
TIN PLATE ON SOLDER FEET.
HOLD DOWNS - TIN PLATE.

△ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.


4. MINIMUM HOST PCB THICKNESS: 1.5.

△ SEE MSA SPECIFICATION FOR ADDITIONAL PADDLE CARD
LAYOUTS COMPATABLE WITH THIS RECEPTACLE AND FOR
OPTIONAL SPLIT CONTACT PAD LAYOUTS FOR THE
PADDLE CARD. SPECIFICATION PINOUT MAY ALSO
DESIGNATE PAD SEQUENCE DIFFERENT FROM ILLUSTRATION.





△ POSITIONS DESIGNATED AS "SIGNAL" ARE REQUIRED
LOCATIONS FOR HIGH SPEED DIFFERENTIAL PAIR
SIGNALING. THESE LOCATIONS MAY ALSO BE USED FOR
SUPPORTING SIDEBAND SIGNALS OR OTHER UTILITY
PURPOSES. POSITIONS DESIGNATED AS "GROUND" ARE
REQUIRED WHEN SUPPORTING HIGH SPEED DIFFERENTIAL
SIGNALS. THESE LOCATIONS MAY ALSO BE USED FOR
SIDEBAND SIGNALS OR OTHER UTILITY PURPOSES.

△ COMPONENT AND TRACE KEEP OUT AREA. EACH EDGE
0.15 MIN FROM EDGE OF HOLE.

△ TAPE AND REEL PACKAGED FOR PICK AND PLACE SMT
PROCESSING, SEE FIGURE 1. POCKET TAPE WIDTH = 56.





SEE SHEET 4
FOR PART TABLE


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 16JAN2018	 TE Connectivity		
		CHK D. HARMON 16JAN2018			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±	NAME RECEPTACLE ASSEMBLY, VERTICAL, 84 POSITION, SLIVER 2.0		
			PRODUCT SPEC 108-130021		
MATERIAL 			APPLICATION SPEC 114-130008		
			SIZE A1		
		WEIGHT -	DRAWING NO. C=2327678		
		CUSTOMER DRAWING		RESTRICTED TO -	
		SCALE 10:1		SHEET 1 OF 4	
				REV C	

PICK AND PLACE TAPE SHOWN
AS TRANSPARENT FOR CLARITY

CONTACT MATING SURFACES






REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 16 JAN 2018	TE Connectivity	
DIMENSIONS: mm		CHK D. HARMON 16 JAN 2018		
	0 PLC	±	NAME	
	1 PLC	±	RECEPTACLE ASSEMBLY, VERTICAL,	
	2 PLC	±	84 POSITION, SLIVER 2.0	
	3 PLC	±	-	
	4 PLC	±	SIZE	
	ANGLES	±	CAGE CODE DRAWING NO	
MATERIAL		FINISH	114-130008	RESTRICTED TO
		WEIGHT	-	-
CUSTOMER DRAWING		SCALE	10:1	SHEET 2 OF 4
		REV	C	

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

RECOMMENDED PCB OUTLINE DIMENSIONS.
TOLERANCE VALUES ARE CRITICAL. PLEASE BE SURE TO DESIGNATE
TOLERANCES TO PCB SUPPLIER TO ENSURE OPTIMIZED FUNCTIONALITY.



VIEW L-L



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 16 JAN 2018	TE Connectivity	
DIMENSIONS:		CHK D. HARMON 16 JAN 2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. HARMON 16 JAN 2018	NAME RECEPTACLE ASSEMBLY, VERTICAL, 84 POSITION, SLIVER 2.0	
	0 PLC	±	PRODUCT SPEC	
	1 PLC	±	108-130021	
	2 PLC	±	APPLICATION SPEC	
	3 PLC	±	114-130008	
MATERIAL		WEIGHT	SIZE A1	CAGE CODE -
FINISH		CUSTOMER DRAWING	SCALE 10:1	SHEET 3 OF 4
			REV C	

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TABLE 1: CONNECTOR CONTACT IDENTIFICATION 

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
10	GROUND	GROUND
11	SIGNAL	SIGNAL
12	SIGNAL	SIGNAL
13	GROUND	GROUND
14	SIGNAL	SIGNAL
15	SIGNAL	SIGNAL
16	GROUND	GROUND
17	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
19	GROUND	GROUND
20	SIGNAL	SIGNAL
21	SIGNAL	SIGNAL
22	GROUND	GROUND
23	SIGNAL	SIGNAL
24	SIGNAL	SIGNAL
25	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND
29	GROUND	GROUND
30	SIGNAL	SIGNAL
31	SIGNAL	SIGNAL
32	GROUND	GROUND
33	SIGNAL	SIGNAL
34	SIGNAL	SIGNAL
35	GROUND	GROUND
36	SIGNAL	SIGNAL
37	SIGNAL	SIGNAL
38	GROUND	GROUND
39	SIGNAL	SIGNAL
40	SIGNAL	SIGNAL
41	GROUND	GROUND
42	GROUND	GROUND





FIGURE 1 
DIRECTION OFF TOP OF REEL
FOR USER UNREELING
SHOWN AS 2327678-1 THRU 2327678-9
SCALE 2:1

3.0±0.1	ALL	0.76µm Au	20	250	YES	200	3-2327678-3
1.2±0.1	ENDS	0.76µm Au	24	250	NO	200	1-2327678-9
		0.38µm Au				100	1-2327678-8
		FLASH Au/PdNi				50	1-2327678-7
1.8±0.1	ENDS	0.76µm Au	24	250	NO	200	1-2327678-6
		0.38µm Au				100	1-2327678-5
		FLASH Au/PdNi				50	1-2327678-4
1.8±0.1	ALL	0.76µm Au	24	250	NO	200	1-2327678-3
		0.38µm Au				100	1-2327678-2
		FLASH Au/PdNi				50	1-2327678-1
1.2±0.1	ENDS	0.76µm Au	20	350	YES	200	2327678-9
		0.38µm Au				100	2327678-8
		FLASH Au/PdNi				50	2327678-7
1.8±0.1	ENDS	0.76µm Au	20	350	YES	200	2327678-6
		0.38µm Au				100	2327678-5
		FLASH Au/PdNi				50	2327678-4
1.8±0.1	ALL	0.76µm Au	20	350	YES	200	2327678-3
		0.38µm Au				100	2327678-2
		FLASH Au/PdNi				50	2327678-1
A	HOLD DOWNS	PLATING	POCKET TAPE PITCH	REEL QUANTITY	PICK AND PLACE TAPE	MATING CYCLES	PART NUMBER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2327678-8](#)