


Thick Film Semi-Precision Metal Glaze™ Power Resistors

GS-3 Series

- Superior surge performance
- Resistance range from 1Ω - 3MΩ
- Standard tolerances of ±1%, ±2%, ±5%
- Power rating of 3W @25°C; 2W @70°C
- Effective as carbon composite replacement



OBSOLETE

 All Pb-free parts comply with EU Directive 2011/65/EU (RoHS2)

Electrical Data

Part Number	Power Rating (Watts)	Resistance Range (Ohms)	Tolerance (±%)	TCR (±ppm/°C)	Maximum Operating Voltage (Volts)	Dielectric Withstanding Voltage (Volts)
GS-3	2.0 (@ 70°C) 3.0 (@ 25°C)	1.0 - 3M	1, 2, 5	50 (>10Ω) 100, 200 (≥ 1Ω)	1000	1000


Environmental Data

Test		Maximum ΔR Limits			
		MIL-R-26	MIL-R-10509D	MIL-R-22684	GS-3
TCR	±ppm/°C	30	100	200	100/50
Load life	%ΔR	0.5	1.0	2.0	2.0
Short term overload	%ΔR	0.20	0.50	0.50	0.20
Moisture	%ΔR	0.20	1.50	1.50	0.40
Temperature Cycling	%ΔR	0.20	0.50	-	0.20
Solder Effect	%ΔR	-	0.50	0.50	0.20
Termination Strength	%ΔR	0.10	0.20	0.50	0.10
Shock	%ΔR	0.10	0.50	0.50	0.10
Vibration	%ΔR	0.10	0.50	0.50	0.10
Operating Temperature		-55°C to +175°C			


General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


Physical Data



Power Derating Chart



Hot Spot Temperature +25°C Ambient



Ordering Data

Sample Part No.	GS	-	3	100	1000	J	LF
IRC Type							
GS = (Fixed Film Resistor High Stability)							
Power Rating							
3 = 3W @ 25°C / 2W @ 70°C							
TCR Characteristics							
50 = ±50 ppm/°C 100 = ±100 ppm/°C 200 = ±200 ppm/°C (available on values greater than 10 ohms)							
Resistance Value							
(100 ohms and greater - First 3 significant digits plus 4th digit multiplier) Example: 100 ohms = 1000, 1000 ohms = 1001, 150,000 ohms = 1503 (Less than 100 ohms - "R" is used to designate decimal) Example: 51 ohms = 51R0, 1 ohm = 1R00, 0.25 ohms = R250							
Tolerance							
F = ±1%, G = ±2%, J = ±5%							
RoHS Compliance							
LF = RoHS-compliant product Omit this code for SnPb finish							

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

[GS3-100-8201-J](#) [GS3-100-1000-J](#) [GS3-100-1004-J](#) [GS3-100-6800-J](#) [GS3-100-1003-J](#) [GS3-100-1001-J](#) [GS3-100-1002-J](#) [GS3-100-22R0-J](#) [GS3-100-47R0J](#) [GS3-100-2701-J](#) [GS3-100-2700-J](#) [GS3-100-5600-J](#) [GS3-100-10R0-J](#) [GS3-100-4700-J](#) [GS3-100-4701-J](#) [GS3-100-7501-J](#) [GS3-100-1500-J](#) [GS31001504J](#) [GS3-100-3303-J](#) [GS3-100-3301-J](#) [GS1001604J](#) [GS3-100-2402-J](#) [GS3T0 39 5%](#) [GS3T0 6.2K 1%](#) [GS3T0 1800 5%](#) [GS3T0 80.6 1%](#) [GS3T0 1.2K 5%TR](#) [GS3T0 20 1%LF](#) [GS3T0 47K 5%TRLF](#) [GS3T0 5.6K 5%TR](#) [GS31001001J664](#) [GS31001501J664](#) [GS31004221F664](#) [GS31006801J664](#) [GS31001002J664](#) [GS31001502J664](#) [GS31001802J664](#) [GS31002002J664](#) [GS31003302J664](#) [GS31006602J664](#) [GS3501134F664](#) [GS31002201J664](#) [GS31003301J664](#) [GS31005621F664](#) [GS31007501J664](#) [GS3T0 7.15K 1%LF](#) [GS31001802G](#) [GS3T0 7.5K 1%](#) [GS31004301J664](#) [GS3T0 2.2K 5%TR](#) [GS3T0 1.62K 1%TR](#) [GS3T0 1.1K 5%TR](#) [GS3T0 100K 5%](#) [GS3T0 51.1K 1%](#) [GS3T0 220K 5%](#) [GS3T0 47.5 1%TR](#) [GS3T0 1 5%TR](#) [GS3T0 1.5K 5%TR](#) [GS3T0 10 5%](#) [GS3T0 100 5%](#) [GS3T0 100K 5%TR](#) [GS3T0 10K 1%TR](#) [GS3T0 10K 5%](#) [GS3T0 12 5%](#) [GS3T0 13K 5%](#) [GS3T0 1502 JTR](#) [GS3T0 150K 5%](#) [GS3T0 18K 5%TR](#) [GS3T0 1K 5%](#) [GS3T0 1K 5%TR](#) [GS3T0 1M 5%TR](#) [GS3T0 2002 JTR](#) [GS3T0 200K 1%TR](#) [GS3T0 22 5%TR](#) [GS3T0 22K 5%](#) [GS3T0 22K 5%TR](#) [GS3T0 24K 5%TR](#) [GS3T0 27 5%](#) [GS3T0 2K 2%](#) [GS3T0 3.3K 5%TR](#) [GS3T0 3.6K 5%TR](#) [GS3T0 33 5%](#) [GS3T0 330 5%](#) [GS3T0 3302 JTR](#) [GS3T0 330K 5%](#) [GS3T0 330K 5%TR](#) [GS3T0 39K 5%](#) [GS3T0 4.22K 1%TR](#) [GS3T0 4.3K 5%TR](#) [GS3T0 4.7K 2%TR](#) [GS3T0 4.7K 5%](#) [GS3T0 47 5%](#) [GS3T0 47 5%TR](#) [GS3T0 47K 5%](#) [GS3T0 5.62K 1%TR](#) [GS3T0 510 5%TR](#) [GS3T0 56 5%](#) [GS3T0 560 5%TR](#) [GS3T0 6.2K 5%](#) [GS3T0 6.8K 5%TR](#)