## 7mm Spot Diameter LED OP207CL



#### Features:

- SMD Configuration
- Emission Spot Size is 7 mm diameter
- High Power Output with Parallel Rays
- Uniform Distribution
- Emitter Source for Encoder Applications



#### **Description:**

The **OP207CL** is a high power IR LED designed for encoder applications. The LED features a small foot print, low profile for a 7 mm beam diameter. Radiance is a collimated, narrow beam emission pattern provides on-axis intensity for excellent coupling efficiency for encoder applications.

#### **Applications:**

- Linear & Rotary Encoder
- Optical Sensors Switches
- Long Range Light Barriers
- Optical Scanning and Edge Sensing
- Automatic Control Systems

#### **Package Dimensions**



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

# **7mm Spot Diameter LED**

### **OP207CL**



### **Electrical Specification**

Absolute Maximum Ratings (T <sub>A</sub> = 25° C unless otherwise noted)				
Storage Temperature Range	-40° C to +105° C			
Operating Temperature Range	-40° C to +105° C			
Reverse Voltage	10 V			
Continuous Forward Current	100 mA			
Power Dissipation <sup>(1)</sup>	190 mW			
Peak Package Body Temperature (Tp) <sup>(2)</sup>	200°C			

Electrical Characteristics (T <sub>A</sub> = 25° C unless otherwise noted)							
SYMBOL	PARAMETER	MIN	ТҮР	МАХ	UNITS	TEST CONDITIONS	
Po	Total Output Radiant Power	10.0	-		mW	I <sub>F</sub> = 50 mA	
Sd	Spot Light Diameter		7.0		mm	$I_{\rm F}$ = 50 mA , measured at 1.5mm from lens tip	
½ θ <sub>ΗΡ</sub>	Half Intensity Beam Angle		2.25		Degree	I <sub>F</sub> = 50 mA	
λ <sub>P</sub>	Wavelength at Peak Emission	840	855	870	nm	I <sub>F</sub> = 100 mA	
V <sub>F</sub>	Forward Voltage		1.5	1.9	V	I <sub>F</sub> = 50 mA	
I <sub>R</sub>	Reverse Leakage Current		-	10	μA	V <sub>R</sub> = 5.0V	
t <sub>r,</sub> t <sub>f</sub>	Rise Time, Fall Time		22		ns	I <sub>F(PEAK)</sub> = 50mA, PW = 10μs, 10% D.C.	

Notes: 1. Derate linearly at 3.42 mW/°C above 60°C.

2. Product designed for hand soldering only. Use SAC solder. No clean flux recommended.

### **Recommended Land Pattern**

Tolerance ± .005 inches



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

# 7mm Spot Diameter LED

**OP207CL** 





#### **Characteristic Curves (typical)**











General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

# 7mm Spot Diameter LED

**OP207CL** 



### **Characteristic Curves (typical)**





IR Camera Image of Emission Spot



TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics: 514.1.19421.456