




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED	11MAY2019	CJV	JW
B		REVISED PER ECO-19-011736	07AUG2019	AP	JW
C		REVISED PER ECO-21-001773	07FEB2021	TX	DZ

△ HOUSING AND CONTACT OVERMOLDS - LCP, UL94-V0, BLACK.
CONTACTS AND HOLD DOWNS - COPPER ALLOY.
PICK AND PLACE TAPE - POLYIMIDE FILM.

△ CONTACTS - GOLD PLATE ON MATING SURFACES,
TIN PLATE ON SOLDER FEET.
HOLD DOWNS - TIN PLATE.

△ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

4. MINIMUM HOST PCB THICKNESS: 1.5.

△ SEE MSA SPECIFICATION FOR ADDITIONAL PADDLE CARD LAYOUTS COMPATABLE WITH THIS RECEPTACLE AND FOR OPTIONAL SPLIT CONTACT PAD LAYOUTS FOR THE PADDLE CARD. SPECIFICATION PINOUT MAY ALSO DESIGNATE PAD SEQUENCE DIFFERENT FROM ILLUSTRATION.


△ POSITIONS DESIGNATED AS "SIGNAL" ARE REQUIRED LOCATIONS FOR HIGH SPEED DIFFERENTIAL PAIR SIGNALING. THESE LOCATIONS MAY ALSO BE USED FOR SUPPORTING SIDEBAND SIGNALS OR OTHER UTILITY PURPOSES. POSITIONS DESIGNATED AS "GROUND" ARE REQUIRED WHEN SUPPORTING HIGH SPEED DIFFERENTIAL SIGNALS. THESE LOCATIONS MAY ALSO BE USED FOR SIDEBAND SIGNALS OR OTHER UTILITY PURPOSES.

△ COMPONENT AND TRACE KEEP OUT AREA. EACH EDGE 0.15 MIN FROM EDGE OF HOLE.

△ TAPE AND REEL PACKAGED FOR PICK AND PLACE SMT PROCESSING, SEE FIGURE 1. POCKET TAPE WIDTH = 44.

△ PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 16JAN2018	TE Connectivity	
DIMENSIONS:		CHK D. HARMON 16JAN2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. HARMON 16JAN2018	NAME	RECEPTACLE ASSEMBLY, VERTICAL, 56 POSITION, SLIVER 2.0
	0 PLC ±.25	PRODUCT SPEC	SIZE	-
	1 PLC ±0.20	108-130021	CAGE CODE	-
	2 PLC ±.	APPLICATION SPEC	DRAWING NO	2327679
	3 PLC ±.	114-130008	RESTRICTED TO	-
	4 PLC ±.	WEIGHT		
MATERIAL	FINISH	CUSTOMER DRAWING	SCALE	10:1
			SHEET	1 OF 4
			REV	C




RECOMMENDED PCB LAYOUT AND KEEP OUT AREA

4805 (3/13)

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB OUTLINE DIMENSIONS.
TOLERANCE VALUES ARE CRITICAL. PLEASE BE SURE TO DESIGNATE
TOLERANCES TO PCB SUPPLIER TO ENSURE OPTIMIZED FUNCTIONALITY.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE CHK D. HARMON APVD D. HARMON	16JAN2018 16JAN2018 16JAN2018	TE TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±0.25 1 PLC ±0.20 2 PLC ±0.20 3 PLC ±0.20 4 PLC ±0.20 ANGLES ±0.25		RECEPTACLE ASSEMBLY, VERTICAL, 56 POSITION, SLIVER 2.0	
MATERIAL		FINISH		SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				A100779	
				SCALE	
				10:1	
				SHEET	
				3 OF 4	
				REV	
				C	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

TABLE 1: CONNECTOR CONTACT IDENTIFICATION 56

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
10	GROUND	GROUND
11	SIGNAL	SIGNAL
12	SIGNAL	SIGNAL
13	GROUND	GROUND
14	SIGNAL	SIGNAL
15	SIGNAL	SIGNAL
16	GROUND	GROUND
17	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
19	GROUND	GROUND
20	SIGNAL	SIGNAL
21	SIGNAL	SIGNAL
22	GROUND	GROUND
23	SIGNAL	SIGNAL
24	SIGNAL	SIGNAL
25	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND




FIGURE 1 8
DIRECTION OFF TOP OF REEL
FOR USER UNREELING
SHOWN AS 2327679-1 THRU 2327679-9
AND 2-2327679-0
SCALE 2:1

1.8±0.1	0.76µm Au	24	250	YES	200	3-2327679-0
3.7±0.1	0.76µm Au	20	250	YES	200	2-2327679-0
3±0.1	0.76µm Au	24	200	NO	200	1-2327679-9
	0.38µm Au				100	1-2327679-8
	FLASH Au/PdNi				50	1-2327679-7
1.2±0.1	0.76µm Au	24	250	NO	200	1-2327679-6
	0.38µm Au				100	1-2327679-5
	FLASH Au/PdNi				50	1-2327679-4
1.8±0.1	0.76µm Au	24	250	NO	200	1-2327679-3
	0.38µm Au				100	1-2327679-2
	FLASH Au/PdNi				50	1-2327679-1
3±0.1	0.76µm Au	20	250	YES	200	2327679-9
	0.38µm Au				100	2327679-8
	FLASH Au/PdNi				50	2327679-7
1.2±0.1	0.76µm Au	20	350	YES	200	2327679-6
	0.38µm Au				100	2327679-5
	FLASH Au/PdNi				50	2327679-4
1.8±0.1	0.76µm Au	20	350	YES	200	2327679-3
	0.38µm Au				100	2327679-2
	FLASH Au/PdNi				50	2327679-1
A	PLATING	POCKET TAPE PITCH	REEL QUANTITY	PICK AND PLACE TAPE	MATING CYCLES	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.25
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

WEIGHT

CUSTOMER DRAWING

DWN C. VALENTINE 16JAN2018
CHK D. HARMON 16JAN2018
APVD D. HARMON 16JAN2018

PRODUCT SPEC 108-130021
APPLICATION SPEC 114-130008

SIZE A1
CAGE CODE 00779
DRAWING NO. 2327679

RESTRICTED TO

TE Connectivity

NAME RECEPTACLE ASSEMBLY, VERTICAL, 56 POSITION, SLIVER 2.0

SCALE 10:1
SHEET 4 OF 4
REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2327679-4](#)