


AMP

WIRE RANGE

6 AWG
STRADED



- 1 WIRE INSULATION DIA
INSULATION SUPPORT "A" 7.87 [.310] MAX.
- 2 WIRE INSULATION DIA
INSULATION SUPPORT "B" 10.54 [.415] MAX.

INSULATION SUPPORT "A"

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600 V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 10.54-16.77mm ² [20,800-33,100] STRADED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 8-30-93	TE TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R. HERSEY 8-30-93				
		APVD B. BARE 8-30-93	NAME SPLICE, BUTT, SINGLE TO MULTIPLE, TERMINYL, WIRE SIZE: 6 AWG			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL COPPER PER ASTM B-152 NYLON, COLOR:BLUE		FINISH TIN PLATE PER ASTM B-545	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-324621
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV F1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[324621](#)