


# SMD Receiver Component

## OPL6000

**Features:**




- Up to 256kbps Operation
- Up to 250klux Ambient Light Immunity
- Output Drive for Interfacing to Microcontroller
- Reverse Gull Wing Design
- Compliant with Smart Power Meter Standard ANSI C12.18
- Compatible with OP181 Emitter Component


**Description:**


The **OPL6000** is a surface mount receiver component incorporating a custom CMOS ASIC. The product features a digital output in a push-pull inverter design. The circuitry provides ambient light immunity while maintaining low power consumption. The ASIC is lead frame mounted and overmolded, incorporating a lens to achieve maximum light coupling ability. In addition, the overmold compound provides visible light rejection. While this part has been designed specifically for the smart power meter industry, other applications are certainly possible.

**Applications:**

- Smart power meter optical port
- Over the air communications


**ESD**  
 (Human Body Model)

**MOISTURE**  
 (Level-4)

**Pb-Free**  
 (RoHS)


Note: The V<sub>DD</sub> and N/C leads are the wider of the four leads as indicated above but also have red strip indicator on the bottom of the leads.

 Dimensions are  $\pm 0.005$  unless otherwise specified

**General Note**


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

**Absolute Maximum Ratings (T<sub>A</sub> = 25° C unless otherwise noted)****Overall Product**

Storage Temperature Range	-55° C to +100° C
Operating Temperature Range	-40° C to +85° C
D.C. Supply Voltage	3.0 - 5.5 V
Output Drive Current	1 mA
Power Dissipation in Active / Inactive Mode <sup>(1)(2)</sup>	30 mW / 5mW <sup>(2)</sup>
Incident Irradiance	250,000 lux
Solder Reflow Temperature <sup>(3)</sup>	260° C

## Notes:

1. Active mode is defined as the state during which time a signal is being received and the output stages are active.  
Inactive mode is defined as the state during which time no signal is being received and the output stages are inactive.
2. Derate linearly at 0.40 mW/°C (active mode) and 0.067 mW/°C (inactive mode) above 25°C. Solder time less than 5 seconds at temperature extreme.
3. Solder time less than 5 seconds at temperature extreme. Solder time within 5° of peak temperature is 20 to 40 seconds.

**Recommended PCB Layout****General Note**

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Electrical Specifications

**Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

SYMBOL	PARAMETER		MIN	TYP	MAX	UNITS	TEST CONDITIONS
$V_{DD}$	Operating Supply Voltage		3.0	3.3	5.5	V	
$I_{DD}$	Supply Current <sub>(1)</sub>	Active Mode	-	-	5	mA	$V_{DD} = 3.0$ to $5.5$ V No load current
		Inactive Mode	-	-	1.0		
PSRR	Power Supply Rejection Ratio		10	-	-	%	$f = 1$ - $1$ MHz, $V_{DD} > 3.0$ V
$E_{eT(+)}$	Positive Going Threshold Irradiance		-	0.100	0.125	$\text{mW/cm}^2$	$V_{DD} = 3.3$ V $I_p = 940$ nm; collimated radiation
$V_{OL}$	Low Level Output Voltage		-	300	400	mV	$V_{DD} = 3.0$ to $5.5$ V, $I_o = 1$ mA $E_e = 0$ mW/cm <sup>2</sup>
$V_{OH}$	High Level Output Voltage		$V_{DD} - 1.0$	-	-	V	$V_{DD} = 3.0$ to $5.5$ V, $I_o = 1$ mA $E_e = 7.5$ mW/cm <sup>2</sup>
$t_r, t_f$	Rise Time, Fall Time		-	-	150	ns	$V_{DD} = 3.3$ V, $f = 1$ kHz $E_e = 7.5$ mW/cm <sup>2</sup>
$t_{PD LH}, t_{PD HL}$	Propagation Delay		-	-	1.0	$\mu\text{s}$	Decouple Cap ( $V_{DD}$ to GND) = $0.1$ $\mu\text{F}$
$I_I$	Input Leakage Current		-10	-	10	$\mu\text{A}$	
$I_o$	Output Drive Current		-	-	1.0	mA	$V_{DD} = 3.3$ V

Notes:

1. Active mode is defined as the state during which time a signal is being received and the output stages are active.  
Inactive mode is defined as the state during which time no signal is being received and the output stages are inactive.

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.




1645 Wallace Drive, Carrollton, TX 75006 | Ph: +1 972 323 2200  
[www.optekinc.com](http://www.optekinc.com) | [www.ttelectronics.com](http://www.ttelectronics.com)

## Supply Current


### Supply Current vs. Supply Voltage




### Supply Current vs. Frequency



### Supply Current vs. Input Power



### Supply Current vs. Temperature




#### General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Rise/Fall Time


### Rise/Fall Time vs. Supply Voltage




### Rise/Fall Time vs. Frequency



### Rise/Fall Time vs. Input Power



### Rise/Fall Time vs. Temperature




#### General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Propagation Delay


### Propagation Delay vs. Supply Voltage




### Propagation Delay vs. Frequency



### Propagation Delay vs. Input Power



### Propagation Delay vs. Temperature




#### General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Pulse Width Distortion


### Pulse Width Distortion vs. Supply Voltage




### Pulse Width Distortion vs. Frequency



### Pulse Width Distortion vs. Input Power





### Pulse Width Distortion vs. Temperature



#### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


## High and Low Level Output Voltage


**General Note**


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Sensitivity


### Low Power Sensitivity vs. Supply Voltage




### Low Power Sensitivity vs. Frequency



### High Power Sensitivity vs. Frequency







### Low Power Sensitivity vs. Temperature



#### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Frequency Response



**Minimum Frequency vs. Supply Voltage**

**Maximum Frequency vs. Supply Voltage**

**Minimum Frequency vs. Temperature**

**Maximum Frequency vs. Temperature**

**General Note**

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## SMD Receiver Component

OPL6000


## Packaging



W	16.00±0.30	P	8.00±0.10	A0	3.33±0.10	B0	8.00±0.10
E	1.75±0.10	P0	4.00±0.10	K0	3.66±0.10	B1	3.73±0.10
F	7.50±0.10	P2	2.00±0.10	K1	2.30±0.10		
T	0.40±0.05	D0	Ø1.50 <sup>+0.10</sup> <sub>-0.00</sub>				

## Notes:

1. Dimensions are in mm.
2. V<sub>DD</sub> and N/C lead (marked with red stripe) is nearest sprocket holes.



## General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TT Electronics:](#)

[OPL6000](#)