


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT — BY —

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			K1	REVISED PER ECO-11-005294	08APR11
					HMR



- 1 WIRE INSULATION DIA: SEE TABLE.
- 2 TONGUE MATERIAL THK: .031 ± .002

OBSOLETE OBSOLETE OBSOLETE OBSOLETE	.115-.170	100	LOOSE PC, BOX	8-328281-1
	.115-.170	100	ON TAPE, SM. BOX	1-328281-4
	.115-.170	1000	ON TAPE, LG. BOX	1-328281-3
	.105-.170	5000	ON TAPE, REEL	1-328281-2
	.115-.170	5000	ON TAPE, REEL	1-328281-1
	.105-.170	5000	LOOSE PIECE	1-328281-0
	.115-.170	—	LOOSE PIECE	328281

	WIRE INS. DIA.	QUANTITY	DESCRIPTION		PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .008 ANGLES ± —	CONTRACT NO		 TE Connectivity		
	DR UTA/RFB 10-4-85				
MATERIAL INSULATION: NYLON - BLUE BODY & SLEEVE: COPPER (CG-C-376) FINISH BODY & SLEEVE TIN PL (MIL-T-10727) .000100 MIN. THK.	CHK P. Mutyalach 2-13-86		NAME		
	APPD C. Maitland 12-13-86		TERMINAL P.I.D.G., SPADE WIRE SIZE: 16-14		
	APPD				
	DSGN APPD		SIZE	FSCM NO	DRAWING NO
	OTHER APPD		B	00779	328281
		SCALE	NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-328281-1](#)