



REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
H6		REVISED PER ECO-15-016493	27NOV2015	NK DR
H7		REVISED PER ECO-17-016703	30MAR2018	RS DR



- 1 STAMP AMP 22-20 APPROX AS SHOWN
- 2 FOR 0.889[.035] TO 2.540[.100] WIRE INSULATION DIA
- 3 BODY MATERIAL THK: 5.842±0.051 [.023±.002]
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 5 BODY: MATERIAL - COPPER ASTM B152  
FINISH - OVER NICKEL PLATE SAE AMS  
SAE AMS QQ-N-290 0.0076[.0003] AVG EXT. THK.
- 6 SLEEVE: MATERIAL - COPPER, ASTM B152  
FINISH - NICKEL PL, SAE AMS QQ-N-290  
0.00076[.00003] AVG EXT. THK
- 7 INSULATION:  
MATERIAL - PTFE ASTM D3295  
COLOR: GREEN
- 8 NOTE DELETED



7	#10	5.004[.197]	100	LOOSE PIECE,BAG	8-50832-1
7	#10	5.004[.197]	2500	50832-1 ON TAPE	50832-3
7	M4 [#8]	4.343[.171]	2500	50832 ON TAPE	50832-2
7	#10	5.004[.197]	1000	LOOSE PIECE	50832-1
7	M4 [#8]	4.343[.171]	1000	LOOSE PIECE	50832
	"B"	"A"	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 288°C [550°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 30JAN03	TE Connectivity Ltd.	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 1°	CHK T MICHIELUTTI 30JAN03		
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-0.65mm² [509-1,290] STRANDED WIRE ONLY			APVD T MICHIELUTTI 30JAN03	NAME TERMINAL, PIDG, STRATO-THERM, RING TONGUE, 22-20 AWG	
TOOLING INFORMATION	1-800-526-5142				PRODUCT SPEC -	SIZE A3	CAGE CODE 00779
FOR ORDER ENTRY			MATERIAL 5 6 7	FINISH 5 6 7	APPLICATION SPEC -	DRAWING NO C=50832	RESTRICTED TO -
			CUSTOMER DRAWING		WEIGHT	SCALE 8:1	SHEET 1 OF 1
						REV H7	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[50832-2](#)