


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-20-013368	25SEP2020	RZ	HL



△ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER  
COLOR: NATURAL.

△ CONTACT MATERIAL: PHOSPHOR BRONZE



△ CONTACT FINISH:(C)  
UNDERPLATE (ENTIRE CONTACT):  
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290  
ON MATING SURFACES  
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA  
UNCONTROLLED ENVIRONMENT.  
ON LEADS:  
0.0005 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.  
LUBRICATION (MIN MATING SURFACES):  
SURFACE CONDITIONER AFTER PLATING.

④ PART MARKING PER TE SPEC 115-9009 LOCATED APPROXIMATELY AS SHOWN BETWEEN RIBS/SLOTS ON EITHER SIDE OF HOUSING AT MANUFACTURER'S DISCRETION.

5 PART TO BE MARKED WITH DATE CODE ONLY.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7 TE OR TE CONNECTIVITY LOGO IS LOCATED.



RECOMMENDED CIRCUIT PATTERN  
PER IPC-D300 TYPE II, CLASS C  
(COMPONENT SIDE)

OBSELETE	82	41	83.88	△	210	<del>5223524-7</del>
	70	35	71.88		180	<del>523524-6</del>
△ OBSELETE	58	29	59.88	△	150	<del>523524-5</del>
	46	23	47.88		120	<del>523524-4</del>
△ OBSELETE	34	17	35.88	△	90	<del>5223524-3</del>
	22	11	23.88	△	60	<del>5223524-2</del>
	10	5	11.88		30	<del>5223524-1</del>
C	B	A	FINISH	NO	OF	PART NUMBER

[illegible]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5223524-7](#)