



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		P3	REVISED PER ECO-12-010411	05JUN12	KH	MM



- 1

HSG. POLYPHENYLENE SULFIDE.
- 2

CONTACT: PHOS BRONZE.
- 3

DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000050-.000100 BRIGHT TIN-LEAD ON SOLDER TINES ALL OVER .000050 NICKEL ENTIRE CONTACT.
- 4

"AMP", "CSA", DATE CODE, AND PART NUMBER MARKED WITH .062±.015 HIGH CHARACTERS. THE ORDER AND LOCATION IS OPTIONAL.
- 5

POINT OF MEASUREMENT FOR PLATING THICKNESS INSIDE BEAMS.
- 6

TOLERANCE NON-CUMULATIVE.
- 7

THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES NOT THE CONTACT LOCATIONS.
- 8



OBSOLETE PART NUMBER.
- 9

PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
- 10

DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000050-.000100 MATTE TIN ON SOLDER TINES ALL OVER .000050 NICKEL ENTIRE CONTACT.
- 11

ROHS 2002/95/EC COMPLIANT.
- 12

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED P.C. BD. LAYOUT

OBSOLETE	10	.500	.858	12	11	6-534972-5
		.700	1.058	16	11	6-534972-4
		7.900	8.258	160	11 8	6-534972-3
		6.900	7.258	140	11 8	6-534972-2
		6.400	6.758	130	11 8	6-534972-1
		5.900	6.258	120	11	6-534972-0
		5.100	5.458	104	11 8	5-534972-9
		4.900	5.258	100	11	5-534972-8
		4.400	4.758	90	11	5-534972-7
		3.900	4.258	80	11	5-534972-6
OBSOLETE	9	3.400	3.758	70	11	5-534972-5
		2.900	3.258	60	11	5-534972-4
		2.400	2.758	50	11	5-534972-3
		1.900	2.258	40	11	5-534972-2
		1.400	1.758	30	11	5-534972-1
		.500	.858	12		1-534972-5
		.700	1.058	16		1-534972-4
		7.900	8.258	160	8	1-534972-3
		6.900	7.258	140	8	1-534972-2
		6.400	6.758	130	8	1-534972-1
OBSOLETE	3	5.900	6.258	120		1-534972-0
		5.100	5.458	104	8	534972-9
		4.900	5.258	100		534972-8
		4.400	4.758	90		534972-7
		3.900	4.258	80		534972-6
		3.400	3.758	70		534972-5
		2.900	3.258	60		534972-4
		2.400	2.758	50		534972-3
		1.900	2.258	40		534972-2
		1.400	1.758	30		534972-1

FINISH	B	A	NO OF POSN	PART NUMBER
--------	---	---	------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SMITH 6-25-87	TE Connectivity	
DIMENSIONS: INCHES		CHK D. SARVER 7-8-87		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. SARVER 7-8-87	NAME RECEPTACLE ASSY, VERTICAL MT, MOD II,.100 x .100CL WITH MTG EARS, SHORT-POINT	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC		
MATERIAL 1 2		WEIGHT -	SIZE A2	CAGE CODE 00779
FINISH SEE TABLE		CUSTOMER DRAWING	DRAWING NO C=534972	RESTRICTED TO -
		SCALE 4:1	SHEET 1 of 1	REV P3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-534972-3](#)