


Power Inductors

Model HM72L-0420 series




Features:

- Operating Temperature Range -55°C to $+125^{\circ}\text{C}$
- Ambient Temperature, Maximum $+85^{\circ}\text{C}$
- Temperature Rise, 40°C
- RoHS Compliant



 All parts are Pb-free and comply with EU Directive 2011/65/EU (RoHS2)

Schematic



Specifications @ 25°C

Part Number	Inductance ($\mu\text{H} \pm 20\%$ @0A)	DCR (m Ω) Typ	DCR (m Ω) Max	I _{rms} (A)	Isat (A)	Part Number	Inductance ($\mu\text{H} \pm 20\%$ @0A)	DCR (m Ω) Typ.	DCR (m Ω) Max	I _{rms} (A)	Isat (A)
HM72L-0420R10LFTR	0.10	3.5	4.0	12.0	22.0	HM72L-04201R2LFTR	1.20	24.0	27.0	4.5	7.0
HM72L-0420R15LFTR	0.15	6.0	6.6	9.0	13.0	HM72L-04201R5LFTR	1.50	38.0	46.0	4.0	6.0
HM72L-0420R22LFTR	0.22	6.0	6.6	9.0	12.5	HM72L-04202R2LFTR	2.20	52.0	58.0	3.0	5.0
HM72L-0420R33LFTR	0.33	9.6	13.0	8.0	12.0	HM72L-04203R3LFTR	3.30	74.0	87.0	2.5	4.0
HM72L-0420R47LFTR	0.47	12.5	14.0	7.0	9.5	HM72L-04204R7LFTR	4.70	98.0	110.0	2.0	3.5
HM72L-0420R56LFTR	0.56	14.0	16.0	6.5	10.0	HM72L-04205R6LFTR	5.60	105.0	115.0	1.8	3.0
HM72L-0420R60LFTR	0.60	14.0	16.0	6.5	10.0	HM72L-04206R8LFTR	6.80	160.0	175.0	1.5	2.5
HM72L-0420R68LFTR	0.68	16.0	18.0	6.0	9.0	HM72L-0420100LFTR	10.0	256.0	282.0	1.2	2.2
HM72L-04201R0LFTR	1.00	24.0	27.0	4.5	7.0						

- Notes:
- (1) Isat is the saturation current at which inductance rolls off approximately 30% from its initial (zero DC)
 - (2) I_{rms} is the approximate current at which $\Delta T = 40^{\circ}\text{C}$
 - (3) Operating Temperature Range -55°C to $+125^{\circ}\text{C}$









General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | BI Technologies

A-1445, Jalan Tanjung Api
25050 Kuantan Pahang Darul Makmur, Malaysia | Ph: +60 9 565 8888
www.ttelectronicsmagnetics.com/customer-service-enquiry









Electrical Specifications @ 25



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Electrical Specifications @ 25°C




General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Power Inductors

Model HM72L-0420 series



Outline dimensions (mm)




CASE SIZE	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	G(mm)	H(mm)
0420 series	4.05 ± 0.25	4.45 ± 0.25	2	1.5 ± 0.3	0.8 ± 0.3	4.95	2.15	2.3

Packaging

Standard:	Embossed Tape and Reel	
	Diameter:	All case size = 13" (330mm))
	Reel:	Case size 0420 = 2,000 units

Ordering information



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

<u>HM72L-0420R15LFTR</u>	<u>HM72L-04205R6LFTR</u>	<u>HM72L-04202R2LFTR</u>	<u>HM72L-04201R2LFTR</u>	<u>HM72L-04203R3LFTR</u>
<u>HM72L-0420R47LFTR</u>	<u>HM72L-04204R7LFTR</u>	<u>HM72L-0420R68LFTR</u>	<u>HM72L-0420R60LFTR</u>	<u>HM72L-0420R33LFTR</u>
<u>HM72L-04206R8LFTR</u>	<u>HM72L-0420R56LFTR</u>	<u>HM72L-04201R0LFTR</u>	<u>HM72L-0420100LFTR</u>	<u>HM72L-0420R22LFTR</u>
<u>HM72L-0420R10LFTR</u>	<u>HM72L-04201R5LFTR</u>			