


Power Inductors


Model HM72L-0624 series




Features:

- Operating Temperature Range -55°C to $+125^{\circ}\text{C}$
- Ambient Temperature, Maximum $+85^{\circ}\text{C}$
- Temperature Rise, 40°C
- RoHS Compliant



 All parts are Pb-free and comply with EU Directive 2011/65/EU (RoHS2)

Schematic



Specifications @ 25°C

| Part Number | Inductance ($\mu\text{H} \pm 20\%$ @0A) | DCR (m Ω) Typ | DCR (m Ω) Max | I _{rms} (A) | I _{sat} (A) | Part Number | Inductance ($\mu\text{H} \pm 20\%$ @0A) | DCR (m Ω) Typ. | DCR (m Ω) Max | I _{rms} (A) | I _{sat} (A) |
|-------------------|------------------------------------------------|-----------------------------|-----------------------------|-------------------------|-------------------------|-------------------|------------------------------------------------|------------------------------|-----------------------------|-------------------------|-------------------------|
| HM72L-0624R10LFTR | 0.10 | 1.5 | 1.7 | 30.0 | 50.0 | HM72L-06242R2LFTR | 2.20 | 28.0 | 34.0 | 6.5 | 14.0 |
| HM72L-0624R22LFTR | 0.22 | 2.9 | 3.2 | 21.0 | 34.0 | HM72L-06243R3LFTR | 3.30 | 36.5 | 51.6 | 5.0 | 13.0 |
| HM72L-0624R33LFTR | 0.33 | 3.7 | 4.1 | 18.0 | 22.0 | HM72L-06244R7LFTR | 4.70 | 45.0 | 63.0 | 4.5 | 9.0 |
| HM72L-0624R47LFTR | 0.47 | 6.0 | 6.5 | 13.5 | 21.0 | HM72L-06245R6LFTR | 5.60 | 66.0 | 73.0 | 4.0 | 8.0 |
| HM72L-0624R68LFTR | 0.68 | 8.7 | 9.4 | 11.0 | 18.0 | HM72L-06246R8LFTR | 6.80 | 72.5 | 95.0 | 3.6 | 7.0 |
| HM72L-0624R82LFTR | 0.82 | 10.6 | 11.8 | 10.0 | 17.0 | HM72L-06248R2LFTR | 8.20 | 95.0 | 106.0 | 3.0 | 6.5 |
| HM72L-06241R0LFTR | 1.00 | 13.1 | 14.2 | 9.0 | 16.0 | HM72L-0624100LFTR | 10.0 | 115.6 | 129.0 | 2.5 | 6.0 |
| HM72L-06241R5LFTR | 1.50 | 18.5 | 21.2 | 7.5 | 15.0 | | | | | | |

- Notes: (1) I_{sat} is the saturation current at which inductance rolls off approximately 30% from its initial (zero DC)
- (2) I_{rms} is the approximate current at which $\Delta T = 40^{\circ}\text{C}$
- (3) Operating Temperature Range -55°C to $+125^{\circ}\text{C}$

General Note









TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | BI Technologies

A-1445, Jalan Tanjung Api
25050 Kuantan Pahang Darul Makmur, Malaysia | Ph: +60 9 565 8888
www.ttelectronicsmagnetics.com/customer-service-enquiry

Issue A 10/2018 Page 1








Electrical Specifications @ 25



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


Electrical Specifications @ 25



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Outline dimensions (mm)




| CASE SIZE | A(mm) | B(mm) | C(mm) | D(mm) | E(mm) | F(mm) | G(mm) | H(mm) |
|-------------|-----------|-----------|-------|-----------|-----------|-------|-------|-------|
| 0624 series | 6.6 ± 0.3 | 7.1 ± 0.3 | 2.4 | 3.0 ± 0.3 | 1.6 ± 0.5 | 7.4 | 3.7 | 3.5 |

Packaging

| | | | | |
|-----------|------------------------|----------|----------------|---------------|
| Standard: | Embossed Tape and Reel | | | |
| | Reel: | Diameter | All case size | = 13" (330mm) |
| | | Capacity | Case size 0624 | = 1,000 units |

Ordering information



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

| | | | | |
|------------------------------------------|------------------------------------------|------------------------------------------|------------------------------------------|------------------------------------------|
| <u>HM72L-06241R0LFTR</u> | <u>HM72L-0624R10LFTR</u> | <u>HM72L-0624R33LFTR</u> | <u>HM72L-06246R8LFTR</u> | <u>HM72L-0624R22LFTR</u> |
| <u>HM72L-06248R2LFTR</u> | <u>HM72L-0624R82LFTR</u> | <u>HM72L-0624R47LFTR</u> | <u>HM72L-0624R68LFTR</u> | <u>HM72L-06242R2LFTR</u> |
| <u>HM72L-06243R3LFTR</u> | <u>HM72L-0624100LFTR</u> | <u>HM72L-06245R6LFTR</u> | <u>HM72L-06244R7LFTR</u> | <u>HM72L-06241R5LFTR</u> |