

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	V2	REVISED PER ECO-16-004223	19JUL2016	NK	MZ

- 1

BRASS PER ASTM B-36.
- 2

2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL.
- 3


SELECTIVELY PLATED 0.76um[.000030] MIN GOLD, FOR A DISTANCE OF 5.08[.200] FROM MATING END, GOLD FLASH ON REMAINDER, ALL OVER 1.27um[.000050] MIN NICKEL.
- 4

GOLD PLATING NOT TO APPEAR ON INSULATION SUPPORT STABILIZER.
- 5

POST WILL ACCEPT (SEE TABLE) TERMINATIONS.
- 6

.000100 MIN TIN OVER .000050 NICKEL. (POST).
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



OBSOLETE	6	3	SPECIAL	35.03 [1.379]	14.86 [.585]	1-66471-9
		3	1	37.97 [1.495]	17.81 [.701]	1-66471-8
		6	3	49.89 [1.964]	29.74 [1.171]	1-66471-7
OBSOLETE	6	6	1	37.97 [1.495]	17.81 [.701]	1-66471-6
		3	3	49.89 [1.964]	29.74 [1.171]	1-66471-5
OBSOLETE	2	3	SPECIAL	35.03 [1.379]	14.86 [.585]	1-66471-4
		2	SPECIAL	40.79 [1.606]	20.65 [.813]	1-66471-0
		3	3	49.89 [1.964]	29.74 [1.171]	66471-9
		3	1	37.97 [1.495]	17.81 [.701]	66471-7
		2	3	49.89 [1.964]	29.74 [1.171]	66471-3
		2	1	37.97 [1.495]	17.81 [.701]	66471-1
	POST FINISH	BODY FINISH	NO OF TERM	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.REIFSNYDER
07 JUN 96

CHK
R.STONE
12 JUL 96

APVD
G.A.STEINHAUER
23 JUL 96

TE Connectivity

PIN CONTACT, CRIMPED,
.062 DIA, .045 x .045 POST,

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE CALLOUTS

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25[.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
SEE CALLOUTS

PRODUCT SPEC
APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-66471

RESTRICTED TO
-

SCALE
4:1

SHEET
1 of 1

REV
V2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66471-7](#)