




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

TUSONIX PART NO.	518-000 A 2.5-9
Value:	2.5 - 9 pF
Value Tol.:	MIN. + 10%, MAX. -10% +100%
Temp. Coef.:	NP0
Rating:	100 VDC @ 85°C
Operating Range:	-55°C TO + 125°C
To Tusonix Spec Unless Stated Otherwise	

NOTE:
ALL METAL PARTS SILVER PLATED.

FOR DIMENSIONS ≤ .125"/3.18mm,
TOLERANCE IS ±.015"/0.38mm.
FOR DIMENSIONS ≥ .126"/3.20mm,
TOLERANCE IS ±.015"/0.38mm.

X-2015 Rev-0 REVISION RECORD Original Release C.O. 20021203-1-02	0	TOLERANCES unless otherwise specified		Title	
		2 PLC. DECIMAL ± 		MINIATURE CERAMIC TRIMMER	
		3 PLC. DECIMAL ±			
		ANGLES ± 		Drawn S.M. 12-03-02	
		TUSONIX TUCSON, ARIZONA		Approved T.C. 12-03-02	
				A	518-000 A 2.5-9

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[0518-000-A-2.5-9LF](#)