





Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING **DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING** **DIMENSIONS IN METRIC - []**



NOTE:
ALL METAL PARTS SILVER PLATED.

FOR DIMENSIONS ≤ .125"/3.18mm,
TOLERANCE IS ±.015"/0.38mm.
FOR DIMENSIONS ≥ .126"/3.20mm,
TOLERANCE IS ±.030"/0.76mm.



ORDERING INFORMATION

Part No.	538-011 B 7.0 - 25
Capacitance	7.0 - 25 pF
Capacitance Tol.	MIN . + 10%, MAX. -10%, +100%
Dielectric Type Code	B
Voltage Rating	350 VDC TO + 85°C, 200VDC TO +125°C
Operating Temperature Range:	-55°C TO + 125°C
To Tusonix Spec Unless Stated Otherwise	

X-2015 Rev-0

REVISION RECORD			METRIC DIM'S & ORINATION SYMBOL CIRCUIT & NOTES ADDED L.E. 06-03-03	1	20030530-1-01	TOLERANCES unless otherwise specified		Title CERAMIC TRIMMER				
Original Release C.O. 200001105-7-01		2 PLC. DECIMAL ± 										
		3 PLC. DECIMAL ± 										
		ANGLES ± 10°				Drawn L.E. 01-07-00						
						TUSONIX TUCSON, ARIZONA		Approved H.R. 01-07-00				
								A	538-011 B 7.0 - 25			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[0538-011-B-7.0-25LF](#)