

Features

- ☒ Frequency range : 1MHz to 170MHz
- ☒ SMD seam sealing ceramic package
- ☒ Supply voltage : 1.8V ~ 3.3V
- ☒ CMOS output
- ☒ Tri-state function available
- ☒ External dimensions (mm)
L : 5.0 x W : 3.2 x H : 1.2
- ☒ RoHS compliant & Pb free

Applications

- ☒ Networking, Server, Storage
- ☒ Wireless communications
- ☒ Fibre channel, Ethernet, SATA, SAS, PCI-E, USB, WLAN, xDSL, xPON
- ☒ PC mainboard, Notebook, HDD, SSD, Graphics card, Computer peripherals
- ☒ Audio, Video, Gaming, Printer, DSC, IP CAM, Consumer products


Electrical Characteristics

Item	7C	Conditions
Frequency Range (F_0)	1MHz ~ 170MHz	
Frequency Stability (F_{stab})	± 50 , ± 25 ppm	-10°C ~ +70°C; Note [1]
	± 50 , ± 30 , ± 25 , ± 15 ppm	-40°C ~ +85°C; Note [1]
Operating Temperature Range (T_{OTR})	-10°C ~ +70°C	
	-40°C ~ +85°C	
Supply Voltage (V_{DD})	1.8V, 2.5V, 2.8V, 3.3V	$V_{DD} \pm 10\%$
Current Consumption (I_{DD})	10 mA Max.	1MHz ~ 75MHz
	20 mA Max.	75MHz ~ 170MHz
Output Type	CMOS	
Output Load (C_L)	15 pF	
Output Voltage High (V_{OH})	90% V_{DD} Min.	
Output Voltage Low (V_{OL})	10% V_{DD} Max.	
Rise & Fall Time (T_r / T_f)	8 ns Max.	10% ~ 90% of V_{DD}
Duty Cycle	40% ~ 60%	
Start-up Time	5 ms Max.	
Enable Voltage High, Logic "1"	70% V_{DD} Min.	Input to Pin1 Note [2]
Enable Voltage Low, Logic "0"	30% V_{DD} Max.	
Phase Jitter, RMS	1 ps Max.	Note [3]
Aging (F_{aging})	± 3 ppm Max.	at 25°C ± 3 °C, first year
Storage Temperature Range (T_{STR})	-55°C ~ +125°C	

Notes:

- [1] Inclusive of frequency tolerance at 25°C, 1st year aging at 25°C, and variations over operating temperature, supply voltage, and load.
- [2] Output will be enabled if Pin1 is Logic "1" or open; Output will be disabled if Pin1 is Logic "0".
- [3] Freq. 10MHz~40MHz, integrated 12kHz~5MHz; Freq. >40MHz, integrated 12kHz~20MHz.

Dimensions



(Unit: mm)

Ordering Information

B ± 50 ppm (-10°C ~ +85°C)
C ± 100 ppm (-10°C ~ +70°C)
F ± 100 ppm (-40°C ~ +85°C)

7C - 30.000M B E - T

Frequency in Hz

Please contact us for available frequencies

Packaging Method

T Tape & Reel


Supply Voltage

B 3.3 V
E 2.8 V
C 2.5 V
D 1.8 V

Frequency Stability

A ± 25 ppm (-10°C ~ +70°C)
D ± 25 ppm (-40°C ~ +85°C)
E ± 50 ppm (-40°C ~ +85°C)


Packing



Reflow Profile

Solder melting point : $220^\circ\text{C} \pm 10^\circ\text{C}$, 60 sec. Min.

Peak temperature : $260^\circ\text{C} \pm 10^\circ\text{C}$, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[7C-12.000MBA-T](#) [7C-16.000MBA-T](#) [7C-20.000MBA-T](#) [7C-24.000MBA-T](#) [7C-24.576MBA-T](#) [7C-25.000MBA-T](#) [7C-26.000MBA-T](#) [7C-4.000MBA-T](#) [7C-40.000MBA-T](#) [7C-44.000MBA-T](#) [7C-48.000MBA-T](#) [7C-50.000MBA-T](#) [7C-6.000MBA-T](#) [7C-8.000MBA-T](#) [7C-20.000MDA-T](#) [7C-24.000MDA-T](#) [7C-24.576MDA-T](#) [7C-26.000MDA-T](#) [7C-27.000MBA-T](#) [7C-40.000MDA-T](#) [7C-48.000MDA-T](#) [7C-19.200MCA-T](#) [7C-2.048MBE-T](#) [7C-14.000MBE-T](#) [7C-8.000MBE-T](#) [7C-7.3728MBE-T](#) [7C-40.000MBE-T](#) [7C-48.000MBE-T](#) [7C-66.000MBE-T](#) [7C-25.000MBE-T](#) [7C-156.250MBE-T](#) [7C-33.330MBE-T](#) [7C-125.000MBE-T](#) [7C-75.000MBE-T](#) [7C-20.000MBE-T](#) [7C-42.150MBE-T](#) [7C-12.270MBE-T](#) [7C-28.63636MBE-T](#) [7C-6.144MBA-T](#) [7C-77.760MBE-T](#) [7C-6.144MBE-T](#) [7C-10.000MBE-T](#) [7C-100.000MBE-T](#) [7C-33.000MBE-T](#) [7C-2.176MBE-T](#) [7C-66.667MBE-T](#) [7C-27.000MBE-T](#) [7C-24.576MBE-T](#) [7C-12.000MBE-T](#) [7C-62.500MBE-T](#) [7C-125.000MBA-T](#) [7C-12.288MBE-T](#) [7C-30.000MBE-T](#) [7C-24.000MBE-T](#) [7C-8.192MBE-T](#) [7C-50.000MBE-T](#) [7C-45.000MBA-T](#) [7C-1.000MBA-T](#) [7C-1.000MBD-T](#) [7C-8.192MBD-T](#) [7C-9.8304MBA-T](#) [7C-9.8304MBD-T](#) [7C-66.667MBD-T](#) [7C-75.000MDE-T](#) [7C-8.192MBA-T](#) [7C-66.6667MDE-T](#) [7C-66.667MBA-T](#) [7C-38.400MDA-T](#) [7C-40.000MBD-T](#) [7C-48.000MDE-T](#) [7C-50.000MBD-T](#) [7C-33.3330MBD-T](#) [7C-33.3330MBE-T](#) [7C-33.3330MDE-T](#) [7C-2.048MBD-T](#) [7C-24.000MBD-T](#) [7C-24.000MDE-T](#) [7C-25.000MBD-T](#) [7C-25.000MDE-T](#) [7C-15.000MBA-T](#) [7C-15.000MBD-T](#) [7C-15.000MBE-T](#) [7C-2.048MBA-T](#) [7C-133.000MBE-T](#) [7C-133.3330MDE-T](#) [7C-1.000MBE-T](#) [7C-100.000MBD-T](#) [7C-100.000MDE-T](#) [7C-80.000MEA-T](#) [7C-28.63636MDE-T](#)