

Features

Frequency range : 1MHz to 133MHz
 SMD seam sealing ceramic package
 Supply voltage : 1.8V ~ 3.3V
 CMOS output
 Tri-state function available
 External dimensions (mm)
 L : 3.2 x W : 2.5 x H : 1.0
 RoHS compliant & Pb free

Applications

Networking, Server, Storage
 Wireless communications
 Fibre channel, Ethernet, SATA, SAS,
 PCI-E, USB, WLAN, xDSL, xPON
 PC mainboard, Notebook, HDD, SSD,
 Graphics card, Computer peripherals
 Audio, Video, Gaming, Printer, DSC,
 IP CAM, Consumer products


Electrical Characteristics

Item	7X	Conditions
Frequency Range (F_0)	1MHz ~ 133MHz	
Frequency Stability (F_{stab})	± 50 , ± 25 ppm	-10°C ~ +70°C; Note [1]
	± 50 , ± 25 , ± 20 ppm	-40°C ~ +85°C; Note [1]
Operating Temperature Range (T_{OTR})	-10°C ~ +70°C	
	-40°C ~ +85°C	
Supply Voltage (V_{DD})	1.8V, 2.5V, 3.3V	$V_{DD} \pm 10\%$
Current Consumption (I_{DD})	10 mA Max.	1MHz ~ 75MHz
	15 mA Max.	75MHz ~ 133MHz
Output Type	CMOS	
Output Load (C_L)	15 pF	
Output Voltage High (V_{OH})	90% V_{DD} Min.	
Output Voltage Low (V_{OL})	10% V_{DD} Max.	
Rise & Fall Time (T_r / T_f)	8 ns Max.	10% ~ 90% of V_{DD}
Duty Cycle	45% ~ 55%	
Start-up Time	5 ms Max.	
Enable Voltage High, Logic "1"	70% V_{DD} Min.	Input to Pin1 Note [2]
Enable Voltage Low, Logic "0"	30% V_{DD} Max.	
Phase Jitter, RMS	1 ps Max.	Note [3]
Aging (F_{aging})	± 3 ppm Max.	at 25°C $\pm$ 3°C, first year
Storage Temperature Range (T_{STR})	-55°C ~ +125°C	

Notes:

- [1] Inclusive of frequency tolerance at 25°C, 1st year aging at 25°C, and variations over operating temperature, supply voltage, and load.
- [2] Output will be enabled if Pin1 is Logic "1" or open; Output will be disabled if Pin1 is Logic "0".
- [3] Freq. 10MHz~40MHz, integrated 12kHz~5MHz; Freq. >40MHz, integrated 12kHz~20MHz.

Dimensions



Ordering Information

7X - 30.000M B E - T

Frequency in Hz

Please contact us for available frequencies

Packaging Method

T Tape & Reel


Supply Voltage

B 3.3 V
C 2.5 V
D 1.8 V

Frequency Stability

A ± 25 ppm (-10°C ~ +70°C)
D ± 25 ppm (-40°C ~ +85°C)
E ± 50 ppm (-40°C ~ +85°C)


Packing



Reflow Profile

Solder melting point : $220^\circ\text{C} \pm 10^\circ\text{C}$, 60 sec. Min.

Peak temperature : $260^\circ\text{C} \pm 10^\circ\text{C}$, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[7X-1.8432MBA-T](#) [7X-12.000MBA-T](#) [7X-14.31818MBA-T](#) [7X-19.200MBA-T](#) [7X-20.000MBA-T](#) [7X-24.576MBA-T](#) [7X-25.000MBA-T](#) [7X-26.000MBA-T](#) [7X-30.000MBA-T](#) [7X-38.400MBA-T](#) [7X-48.000MBA-T](#) [7X-40.000MBA-T](#) [7X-14.7456MBE-T](#) [7X-30.000MBE-T](#) [7X-24.576MBE-T](#) [7X-16.000MBE-T](#) [7X-10.000MBE-T](#) [7X-25.000MBE-T](#) [7X-8.000MBE-T](#) [7X-26.000MBE-T](#) [7X-48.000MBE-T](#) [7X-20.000MBE-T](#) [7X-27.000MBE-T](#) [7X-40.000MBE-T](#) [7X-24.000MBE-T](#) [7X-33.000MBE-T](#) [7X-50.000MBE-T](#) [7X-12.000MBE-T](#) [7X-14.31818MBE-T](#) [7X-11.2896MBE-T](#) [7X-66.000MBE-T](#) [7X-100.000MBE-T](#) [7X-16.384MBE-T](#) [7X-66.667MBE-T](#) [7X-125.000MBE-T](#) [7X-12.288MBE-T](#) [7X-19.200MBE-T](#) [7X-19.440MBE-T](#) [7X-8.000MBA-T](#) [7X-8.192MBA-T](#) [7X-80.000MBA-T](#) [7X-66.000MDE-T](#) [7X-7.37280MBA-T](#) [7X-7.3728MBD-T](#) [7X-7.3728MBE-T](#) [7X-50.000MDD-T](#) [7X-50.000MDE-T](#) [7X-60.000MBA-T](#) [7X-48.000MDD-T](#) [7X-48.000MDE-T](#) [7X-50.000MDA-T](#) [7X-40.000MDD-T](#) [7X-40.000MDE-T](#) [7X-48.000MBD-T](#) [7X-48.000MDA-T](#) [7X-4.096MBE-T](#) [7X-40.000MBD-T](#) [7X-40.000MDA-T](#) [7X-35.328MBD-T](#) [7X-37.125MDE-T](#) [7X-38.400MBD-T](#) [7X-38.400MDA-T](#) [7X-33.3330MBA-T](#) [7X-33.3330MBE-T](#) [7X-35.328MBA-T](#) [7X-3.6864MBE-T](#) [7X-30.000MBD-T](#) [7X-32.000MBA-T](#) [7X-32.000MBD-T](#) [7X-33.000MBA-T](#) [7X-27.000MDD-T](#) [7X-27.000MDE-T](#) [7X-3.6864MBA-T](#) [7X-26.000MDD-T](#) [7X-26.000MDE-T](#) [7X-27.000MBA-T](#) [7X-27.000MDA-T](#) [7X-25.000MDA-T](#) [7X-25.000MDD-T](#) [7X-25.000MDE-T](#) [7X-26.000MBD-T](#) [7X-26.000MDA-T](#) [7X-24.000MDA-T](#) [7X-24.000MDD-T](#) [7X-24.000MDE-T](#) [7X-20.480MBD-T](#) [7X-22.5792MBA-T](#) [7X-22.5792MBE-T](#) [7X-24.000MBA-T](#) [7X-2.048MBA-T](#) [7X-20.000MDE-T](#) [7X-20.480MBA-T](#) [7X-16.000MBA-T](#) [7X-16.384MBA-T](#) [7X-16.384MBD-T](#) [7X-19.200MDA-T](#) [7X-12.500MDE-T](#) [7X-13.000MDA-T](#) [7X-14.31818MBD-T](#) [7X-12.288MBA-T](#)