

D

C

B

A



"F" = GOLD AREA

DIMENSION					PART- NO.			PART- NO.			PART- NO.		
					SELECTIVE GOLD PLATED			TIN PLATED			SELECTIVE GOLD PLATED		
A	B	C	F	-	1	5	7	WEIGHT POS. PER ROW			3	4	7
12.7	6.7	3.2	4.4	-	826629			826926					
12.0	6.7	2.5	4.4	-	826630			826935					
11.8	5.8	3.2	4.4	-	826646			826936			829070		
11.1	5.8	2.5	4.4	-	826647			826937					
14.0	8.0	3.2	4.4	-	826648			826938					
13.3	8.0	2.5	4.4	-	826649			826939					
12.7	6.7	3.2	5.5	-	-			-			828356		

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- 1 MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B" SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 2 MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL
- 3 MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B" SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 4 COLOR OF HOUSING: GREY
- 5 COLOR OF HOUSING: GREEN
- 6 TOLERANCES NOT CUMULATIVE
- 7 THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO. EG: 2-826629-0 = 20 POSITIONS
THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.0654 g = 1.308 g
- 8 OBSOLETE

SCALE 8:1
LAYOUT FOR HOLES ON PCB

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

6

±

-

DWN G.HOLAUS 10NOV1989

CHK SCHAAERSCHMIDT M.

APVD

PRODUCT SPEC 108-18012

APPLICATION SPEC 114-25011

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT

SIZE A2

CAGE CODE 00779

DRAWING NO C-826629


RESTRICTED TO -

SCALE 5:1

SHEET 1 OF 4

REV AC 1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



DIMENSION					PART-NO.		PART- NO.		PART- NO.	
					SELECTIVE GOLD PLATED		TIN PLATED	WEIGHT POS. PER ROW	SELECTIVE GOLD PLATED	
B	C	D	F	-	1	5	7		3	4
6.7	3.2	1.3	4.4	-	1	5	7	826631	0.0757 g	826947
6.7	2.5	1.3	4.4	-	1	5	7	826651	0.0731 g	826948
5.8	3.2	1.3	4.4	-	1	5	7	826652	0.0726 g	826949
5.8	2.5	1.3	4.4	-	1	5	7	826653	0.0701 g	826950
8.0	3.2	1.3	4.4	-	1	5	7	826654	0.0803 g	826951
8.0	2.5	1.3	4.4	-	1	5	7	826655	0.0777 g	826952
6.7	3.2	1.3	5.5	-	1	5	7	-	-	828419

CONTACT PIN	CuZn	SEE TABLE
CONTACT PIN	CuSn6	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:


- 1 MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B" SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 2 MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL
- 3 MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B" SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 4 COLOR OF HOUSING: GREY
- 5 COLOR OF HOUSING: GREEN
- 6 TOLERANCES NOT CUMULATIVE
- 7 THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO. EG: 2-826631-0 = 20 POSITIONS

THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.0757 g = 1.514 g
- 8 OBSOLETE
- 10 MATING AND SOLDER SIDE : 2µm TIN OVER 1.27µm NICKEL

SCALE 8:1
LAYOUT FOR HOLES ON PCB

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.HOLAUS CHK SCHAAERSCHMIDT M. APVD -		10NOV1989		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		6		NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT			
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ± ± ± ± ± ±		PRODUCT SPEC 108-18012 APPLICATION SPEC 114-25011 WEIGHT -			
MATERIAL SEE TABLE -		-		-		SIZE A2	CAGE CODE 00779	DRAWING NO C-826629	RESTRICTED TO -
CUSTOMER DRAWING						SCALE 5:1	SHEET 3 OF 4	REV AC1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



"F" = GOLD AREA


DIMENSION					PART-NO.		PART- NO.		PART- NO.	
					SELECTIVE GOLD PLATED		TIN PLATED		SELECTIVE GOLD PLATED	
B	C	D	F	-	  	WEIGHT POS. PER ROW	  	WEIGHT POS. PER ROW	  	WEIGHT POS. PER ROW
6.7	3.2	1.3	4.4	-	 826634	0.1646 g	 826953	0.1656 g	 828418	0.1651 g
6.7	2.5	1.3	4.4	-	 826661	0.1597 g	 826954	0.1606 g		
5.8	3.2	1.3	4.4	-	 826662	0.1587 g	 826955	0.1603 g	 829072	0.1587 g
5.8	2.5	1.3	4.4	-	 826663	0.1538 g	 826956	0.1542 g		
8.0	3.2	1.3	4.4	-	 826664	0.1741 g	 826957	0.1749 g		
8.0	2.5	1.3	4.4	-	 826665	0.1687 g	 826958	0.1699 g		

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- 1 MATING SIDE : AREA "F" MIN 0.7 μ m PdNi + MIN 0.1 μ m GOLD
OVER 1.27 μ m NICKEL BY AREA "B"
SOLDER SIDE: MIN 3 μ m TIN OVER 1.27 μ m NICKEL
- 2 MATING AND SOLDER SIDE : MIN 3 μ m TIN OVER 1.27 μ m NICKEL
- 3 MATING SIDE: AREA "F" 0.13 μ m GOLD OVER 1.27 μ m NICKEL
BY AREA "B"
SOLDER SIDE: MIN 3 μ m TIN OVER 1.27 μ m NICKEL
- 4 COLOR OF HOUSING: GREY
- 5 COLOR OF HOUSING: GREEN
- 6 TOLERANCES NOT CUMULATIVE
- 7 THE NUMBER OF POSITION PER ROW HAS TO BE
ADDED TO THE BASE NO. AS A DASH NO.
E.G: 2-826634-0 = 20 POSITIONS

THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR
FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.1646 g = 3.292 g
- 8 OBSOLETE



SCALE 8:1
LAYOUT FOR HOLES ON PCB

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10NOV1989	 TE Connectivity					
		CHR G.HOLAUS						
DIMENSIONS: mm		APVD SCHAARSCHMIDT M.	NAME AMPMODU II PIN HEADER. SINGLE ROW, DUAL ROW. VERTICAL AND RIGHT ANGLE MOUNT					
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm 		PRODUCT SPEC 108-18012						
		APPLICATION SPEC 114-25011						
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		WEIGHT -						
MATERIAL SEE TABLE		SIZE A2		CAGE CODE 00779	DRAWING NO C-826629	RESTRICTED TO -		
-		CUSTOMER DRAWING				SCALE 5:1	SHEET 4 OF 4	REV A1
-								
-								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[826942-6](#)