

Features

- Frequency range : 1MHz to 40MHz
- SMD seam sealing ceramic package
- Supply voltage : 1.8V ~ 3.3V
- CMOS output
- Phase modulation clock function selectable for EMI reduction
- External dimensions (mm)
L : 2.0 x W : 1.6 x H : 0.76
- RoHS compliant & Pb free

Applications

- Imaging & Display Devices
- HD Camera, DVR
- HD Surveillance Camera
- Computer Peripherals
- Consumer products

Electrical Characteristics

Item		QTM216E	Conditions
Frequency Range (F_0)		1MHz ~ 40MHz	
Frequency Stability (F_{stab})		±50 ppm	Note [1] & [2]
Operating Temperature Range (T_{OTR})		-40°C ~ +85°C	
		-40°C ~ +105°C	
		-40°C ~ +125°C	
Supply Voltage (V_{DD})		1.8V, 2.5V, 3.3V	$V_{DD} \pm 5\%$
Current Consumption (I_{DD})		10 mA Max.	
Output Type		CMOS	
Output Load (C_L)		15 pF	
Output Voltage High (V_{OH})		80% V_{DD} Min.	
Output Voltage Low (V_{OL})		20% V_{DD} Max.	
Rise & Fall Time (T_r / T_f)		8 ns Max.	20% ~ 80% of V_{DD}
Duty Cycle		45% ~ 55%	
Start-up Time		1 ms Max.	
Phase Jitter, RMS		1 ps Max.	Note [2] Integrated 12kHz~5MHz.
Phase Modulation Clock Mode	Enable	30% V_{DD} Max. (Logic "0")	Input to Pin1; Note [3]
	Disable	70% V_{DD} Min. (Logic "1")	
Aging (F_{aging})		±3 ppm Max.	at 25°C±3°C, first year
Storage Temperature Range (T_{STR})		-55°C ~ +125°C	

Notes:

- [1] Inclusive of frequency tolerance at 25°C, variations over operating temperature, supply voltage, load and 1st year aging at 25°C.
- [2] Phase modulation clock mode is disabled.
- [3] Phase modulation clock mode will be enabled if Pin1 is Logic "0"; Phase modulation clock mode will be disabled if Pin1 is Logic "1" or open (Internal pull-high resistor).


Phase Modulation Mode Deviation [4]

Frequency (MHz)	Deviaton range (%)		
	V _{DD} 1.8V	V _{DD} 2.5V	V _{DD} 3.3V
20	± 0.54	± 0.36	± 0.29
24	± 0.62	± 0.42	± 0.34
25	± 0.65	± 0.45	± 0.35
27	± 0.70	± 0.54	± 0.40


Notes:

[4] Contact us for available frequencies and deviation range.


Dimensions



Ordering Information




Packing



DIMENSIONS	A	B	C	D	E	F	G	H
	0.90 ±0.10	2.30 ±0.10	1.90 ±0.10	4.00 ±0.10	8.00 ±0.20	4.00 ±0.10	1.55 ±0.05	1.75 ±0.10

(Unit: mm)




DIMENSIONS	L	L1	W	W1
	178 ±1.00	60.2 ±0.50	11.5 ±0.2	8 +1/-0

(Unit: mm)

Reflow Profile

Solder melting point : 220°C ± 10°C, 60 sec. Min.

Peak temperature : 260°C ± 10°C, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[QTM216E-24.576MDM-T](#) [QTM216E-37.400MBM-T](#) [QTM216E-37.400MDM-T](#) [QTM216E-20.000MBJ-T](#) [QTM216E-20.000MDM-T](#) [QTM216E-24.576MBJ-T](#) [QTM216E-24.000MDE-T](#) [QTM216E-30.000MBE-T](#) [QTM216E-37.400MBJ-T](#) [QTM216E-38.400MDJ-T](#) [QTM216E-40.000MBE-T](#) [QTM216E-24.000MCJ-T](#) [QTM216E-25.000MCM-T](#) [QTM216E-33.333MDM-T](#) [QTM216E-24.576MDJ-T](#) [QTM216E-30.000MDJ-T](#) [QTM216E-24.000MCE-T](#) [QTM216E-25.000MBM-T](#) [QTM216E-25.000MCJ-T](#) [QTM216E-30.000MCE-T](#) [QTM216E-24.000MCM-T](#) [QTM216E-37.400MBE-T](#) [QTM216E-40.000MBJ-T](#) [QTM216E-25.000MBE-T](#) [QTM216E-33.333MCM-T](#) [QTM216E-40.000MCE-T](#) [QTM216E-30.000MCJ-T](#) [QTM216E-30.000MDM-T](#) [QTM216E-33.333MDE-T](#) [QTM216E-38.400MBM-T](#) [QTM216E-38.400MDE-T](#) [QTM216E-24.576MCJ-T](#) [QTM216E-27.000MCJ-T](#) [QTM216E-33.333MBE-T](#) [QTM216E-38.400MBJ-T](#) [QTM216E-37.400MDJ-T](#) [QTM216E-40.000MDM-T](#) [QTM216E-20.000MDJ-T](#) [QTM216E-24.576MBM-T](#) [QTM216E-33.333MBM-T](#) [QTM216E-33.333MCE-T](#) [QTM216E-25.000MBJ-T](#) [QTM216E-25.000MCE-T](#) [QTM216E-30.000MBM-T](#) [QTM216E-20.000MCE-T](#) [QTM216E-20.000MDE-T](#) [QTM216E-24.576MCE-T](#) [QTM216E-27.000MBM-T](#) [QTM216E-27.000MCE-T](#) [QTM216E-40.000MDJ-T](#) [QTM216E-25.000MDE-T](#) [QTM216E-30.000MDE-T](#) [QTM216E-37.400MDE-T](#) [QTM216E-38.400MCJ-T](#) [QTM216E-30.000MBJ-T](#) [QTM216E-38.400MDM-T](#) [QTM216E-24.000MBJ-T](#) [QTM216E-24.576MDE-T](#) [QTM216E-25.000MDM-T](#) [QTM216E-38.400MBE-T](#) [QTM216E-24.000MDM-T](#) [QTM216E-27.000MDE-T](#) [QTM216E-37.400MCJ-T](#) [QTM216E-40.000MCJ-T](#) [QTM216E-24.000MDJ-T](#) [QTM216E-24.576MBE-T](#) [QTM216E-30.000MCM-T](#) [QTM216E-33.333MDJ-T](#) [QTM216E-40.000MCM-T](#) [QTM216E-20.000MCJ-T](#) [QTM216E-20.000MCM-T](#) [QTM216E-24.576MCM-T](#) [QTM216E-27.000MBJ-T](#) [QTM216E-33.333MBJ-T](#) [QTM216E-40.000MDE-T](#) [QTM216E-27.000MDM-T](#) [QTM216E-33.333MCJ-T](#) [QTM216E-40.000MBM-T](#) [QTM216E-38.400MCE-T](#) [QTM216E-20.000MBM-T](#) [QTM216E-24.000MBE-T](#) [QTM216E-24.000MBM-T](#) [QTM216E-27.000MCM-T](#) [QTM216E-27.000MDJ-T](#) [QTM216E-37.400MCE-T](#) [QTM216E-20.000MBE-T](#) [QTM216E-25.000MDJ-T](#) [QTM216E-27.000MBE-T](#) [QTM216E-37.400MCM-T](#) [QTM216E-38.400MCM-T](#)