


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		B1	REVISED PER ECO-11-005027	11MAR11	RK HMR



SPECIFICATIONS:

LAMP DISSIPATION: 1.2W MAX.

INSULATION RESISTANCE: 100 MEGOHMS MIN.

DIELECTRIC STRENGTH: 2000 VAC.

OPERATING TEMPERATURE: -20°C TO +50°C
(-4°F TO +122°F).

NOTES:

- LAMP IS T 3/4 MIDGET FLANGE BASE TYPE (LAMP NOT SUPPLIED).
- 164 IS NON-DILTIGHT SERIES, 165 IS DILTIGHT SERIES.
- VIEWS INCLUDE PLASTIC SHROUDS FOR AVAILABLE LENS SETS, (NOT SUPPLIED).

4 THE PLATINGS CONTAINED IN THIS PART SHALL CONTAIN NO LEAD.

5 PRELIMINARY PART, NOT RELEASED FOR PRODUCTION.

1571542-4	165TZ	4 5
1571542-3	164TZ	
1571542-2	164SZ	
1571542-1	164EZ	
5-1437569-9	165TZ	
5-1437569-3	165SZ	
4-1437569-6	165EZ	
4-1437569-1	164TZ	
3-1437569-2	164SZ	
1437569-8	164EZ	
PART No.	MODEL NUMBER	COMMENTS

REF AUGAT 81091

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S KIRCORIAN 5-18-94	TE Connectivity			
DIMENSIONS: INCHES		CHK W THIA 5-19-94				
		APVD W THIA 5-19-94	NAME PILOT LIGHT 164/165 Z			
		PRODUCT SPEC				
MATERIAL -		APPLICATION SPEC	SIZE A2		CAGE CODE 00779	DRAWING NO C=2-1437569-4
		FINISH -	WEIGHT -		RESTRICTED TO -	SCALE NTS
			CUSTOMER DRAWING		SHEET 1 OF 1	REV B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[164EZ](#)