

D

C

B

A

D

C

B

A

NOTES:

MATERIAL:  
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.  
TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.  
SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.

ELECTRICAL:  
UL CLASS C: 20A, 150V.  
UL CLASS D: 10A, 300V.  
CSA TYPE B: 20A, 300V.  
CSA TYPE C: 20A, 300V.  
CSA TYPE D: 10A, 300V.  
CSA TYPE E: 20A, 300V.  
WIRE RANGE: 12-22 AWG

MECHANICAL:  
MAXIMUM TORQUE RATING: 7 IN-LBS.  
RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS OTHERWISE STATED.

- 1
- SCREWS ARE BOTTOMED, NO THREAD INTERRUPT.

2

3

4


5

6

7

8

<div><div>8</div><div>5</div></div>	.160	4DB-P108-04-SPCL	1.365	4	3-796658-0
	.160	4DB-P108-03-SPCL	1.040	3	2-796658-9
<div><div>8</div></div>	.160	4DB-P108-30	9.815	30	5-1437667-5
<div><div>8</div></div>	.160	4DB-P108-29	9.490	29	796658-9
<div><div>8</div></div>	.160	4DB-P108-28	9.165	28	5-1437667-3
<div><div>8</div></div>	.160	4DB-P108-27	8.840	27	796658-8
<div><div>8</div></div>	.160	4DB-P108-26	8.515	26	5-1437667-2
<div><div>8</div></div>	.160	4DB-P108-25	8.190	25	796658-7
<div><div>8</div></div>	.160	4DB-P108-24	7.865	24	5-1437667-0
<div><div>8</div></div>	.160	4DB-P108-23	7.540	23	796658-6
<div><div>8</div></div>	.160	4DB-P108-22	7.215	22	4-1437667-8
<div><div>8</div></div>	.160	4DB-P108-21	6.890	21	796658-2
<div><div>8</div></div>	.160	4DB-P108-20	6.565	20	4-1437667-6
<div><div>8</div></div>	.160	4DB-P108-19	6.240	19	4-1437667-5
<div><div>8</div></div>	.160	4DB-P108-18	5.915	18	4-1437667-4
<div><div>5</div><div>4</div></div>	.160	4DB-P108-16-105	5.590	17	2-796628-4
<div><div>8</div></div>	.160	4DB-P108-17	5.590	17	4-1437667-2
<div><div>8</div></div>	.160	4DB-P108-16	5.265	16	4-1437667-0
<div><div>8</div></div>	.160	4DB-P108-15	4.940	15	3-1437667-9
<div><div>2</div><div>1</div></div>	.160	4DB-P108-14-102	4.615	14	2-796658-5
	.160	4DB-P108-14-102	4.615	14	2-796658-3
<div><div>2</div></div>	.160	4DB-P108-14	4.615	14	3-1437667-8
	.160	4DB-P108-13	4.290	13	3-1437667-7
	.160	4DB-P108-12	3.965	12	3-1437667-6
	.160	4DB-P108-11	3.640	11	3-1437667-5
	.160	4DB-P108-10	3.315	10	3-1437667-3
	.160	4DB-P106-09-094	2.990	9	1-796658-7
	.160	4DB-P108-09	2.990	9	3-1437667-2
<div><div>5</div><div>2</div></div>	.160	4DB-P108-08-091	2.665	8	1-796658-4
	.160	4DB-P108-08	2.665	8	3-1437667-1
<div><div>3</div><div>2</div></div>	.160	4DB-P106-07-100	2.340	7	2-796658-2
<div><div>3</div><div>2</div></div>	.160	4DB-P106-07-093	2.340	7	1-796658-6
	.160	4DB-P108-07	2.340	7	3-1437667-0
<div><div>3</div><div>2</div></div>	.160	4DB-P106-06-099	2.015	6	2-796658-1
<div><div>6</div><div>1</div></div>	.160	4DB-P108-06-090	2.015	6	1-796658-3
<div><div>8</div><div>5</div></div>	.200	4DB-P108-06	2.015	6	2-796658-6
<div><div>3</div><div>2</div></div>	.160	4DB-P108-06	2.015	6	2-1437667-9
	.160	4DB-P106-05-098	1.690	5	2-796658-0
<div><div>6</div><div>1</div></div>	.160	4DB-P108-05-093	1.690	5	1-796658-5
	.160	4DB-P108-05	1.690	5	2-1437667-8
<div><div>3</div><div>2</div></div>	.160	4DB-P106-04-097	1.365	4	1-796658-9
<div><div>1</div></div>	.160	4DB-P108-04-089	1.365	4	1-796658-2
<div><div>7</div></div>	.160	4DB-P108-04	1.365	4	2-1437667-6
	.160	4DB-P106-03-096	1.040	3	1-796658-8
	.160	4DB-P108-03-088	1.040	3	1-796658-1
	.160	4DB-P108-03	1.040	3	2-1437667-5
	.142	4DB-P108-02-143	.715	2	2-796658-8
<div><div>7</div></div>	.142	4DB-P108-02-142	.715	2	2-796658-7
	.160	4DB-P108-02	.715	2	2-1437667-4
	DIM B	CATALOG NUMBER	DIM A	NO OF POS.	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± .01

3 PLC ± .005

4 PLC ± -

ANGLES ± 1°

FINISH

MATERIAL

-

DWN S WELDON

CHK S YODER

APVD S YODER

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

01MAY2003

5/1/03

5/1/03

NAME

ASSEMBLY, DUAL BARRIER

4DB P108 XX

SIZE A2

CAGE CODE 00779

DRAWING NO C-2-1437667-4

RESTRICTED TO

SCALE NTS

SHEET 1 of 1

REV N8

TE Connectivity

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4DB-P108-12](#)