



Molded Parts Specification Control Drawing

Part Number : 202G6XX
Description : Uni-Boot

NOTES

1. All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$
 2. Dimensions appearing in table are as follows:
a - As Supplied
b - After Unrestricted Recovery
 3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
-  Do not measure wall thickness in convoluted or transition area.



| PART NUMBER | H | | J | | K | P | JO | HW | JW | S | T | B |
|-------------|----------------|----------------|----------------|---------------|----------------|-----------------|----------------|--------------|--------------|--------------|--------------|----------------|
| | Min | Max | Min | Max | Max | ±10% | ±10% | Ref | Ref | Ref | Ref | Nom |
| | a | b | a | b | b | b | b | b | b | b | b | b |
| 202G611 | .56 [14,2] | .27 [6,9] | .44 [11,2] | .19 [4,8] | .83 [21,1] | 4.75 [120,7] | .69 [17,5] | .04 [1,0] | .03 [0,7] | .04 [1,0] | .05 [1,3] | 2.46 [62,5] |
| 202G621 | 1.05 [26,6] | .46 [11,7] | 1.05 [26,6] | .32 [8,1] | 1.05 [26,6] | 5.27 [133,8] | .78 [19,9] | .04 [1,0] | .03 [0,7] | .04 [1,0] | .05 [1,3] | 2.67 [67,8] |
| 202G632 | 1.30 [33,0] | .69 [17,5] | 1.30 [33,0] | .50 [12,7] | 1.29 [32,7] | 5.95 [151,1] | .88 [22,4] | .04 [1,0] | .03 [0,7] | .04 [1,0] | .05 [1,3] | 2.89 [73,4] |
| 202G642 | 1.40 [35,5] | .88 [22,3] | 1.40 [35,5] | .69 [17,5] | 1.49 [37,8] | 6.19 [157,2] | 1.00 [25,4] | .05 [1,3] | .04 [1,0] | .05 [1,3] | .05 [1,3] | 3.08 [78,2] |
| 202G653 | 1.68 [42,6] | 1.10 [27,9] | 1.68 [42,6] | .88 [22,4] | 1.69 [42,9] | 6.70 [170,2] | 1.12 [28,4] | .05 [1,3] | .04 [1,0] | .05 [1,3] | .06 [1,5] | 3.26 [82,8] |

tyco
Electronics Raychem

TYCO ELECTRONICS
307 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : H
Date : 12/10/04

Part Number : 202G6XX
Description : Uni-Boot

Molded Parts Specification Control Drawing

Part Number : 202G6XX
Description : Uni-Boot

| COMPATABILITY CHART | | | | | |
|---------------------|------------------------|--------------------|-------------------|---------------|---------------------|
| MATERIAL DASH NO. | MATERIAL DESCRIPTION | RT SPEC | COATING SLASH NO. | COATING S NO. | COATING DESCRIPTION |
| -55 | Fluoropolymer | RT-1330 | N/A | | |
| -780 | Modified Fluoropolymer | RT-700/780 TYPE II | N/A | | |
| -790 | Modified Fluoropolymer | RT-700/790 TYPE II | N/A | | |
| | | | | | |
| | | | | | |
| | | | | | |

ORDERING INFORMATION

Base part number 202G6XX -X -XX /XX -0

Material dash number

(See Compatability Chart)

Modification number

Adhesive slash number

(If necessary, see Compatability Chart)

Color Designator

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

If this document is printed it becomes uncontrolled.
Check for the latest revision.

tyco
Electronics Raychem

TYCO ELECTRONICS
307 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : H
Date : 12/10/04

Part Number : 202G6XX
Description : Uni-Boot

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202G632-55-0](#)