



REVISIONS					
REV	DATE	DESCRIPTION	BY	CHK	APP
G	6-5-17	REV PER ECO 17-007893	CT	DM	



TAPE MOUNTED
-2 ONLY

1. WIRE BARREL WILL ACCEPT #26 - 28 AWG WIRE.
2. CRIMPING TOOL - USE HANDTOOL M22520/2-01 (AMP P/N 601996-1) WITH POSITIONER M22520/2-06 (AMP P/N 601966-4) SEE AMP INSTRUCTION SHEET, IS7516, FOR CRIMPING INSTRUCTIONS.
3. CONTACT CONFORMS TO MIL-C-24308/57-354, EXCEPT NO COLOR CODE AND INSIDE DIAMETER ON CRIMP BARREL IS SMALLER TO ACCEPT #26 - 28 AWG WIRE.
4. INSERTION/EXTRACTION TOOL AMP P/N 91067-1.
5. USE AMP - TAPEMATIC STRIPPER/CRIMPER MACHINE NUMBER 299406-7 WITH FUNNEL NUMBER 125905-2.
6. SLEEVE MAY BE CRIMPED OR DIMPLED ONTO CONTACT BODY.
7. RESTRICTED TO SPACE SYSTEMS LORAL.

7	AS SHOWN	206496-4
5	AS SHOWN EXCEPT EVCEPT ON TAPE	206496-2
2	AS SHOWN	206496-1
REMARKS	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG T. THOMPSON 06-03-94		TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± .005		1 PLC ± .005		F. KINSEY	
2 PLC ± .005		3 PLC ± .005		F. KINSEY	
4 PLC ± .005		5 PLC ± .005		PRODUCT SPEC	
ANGLES		FINISH		APPLICATION SPEC	
MATERIAL SEE CALLOUT		WEIGHT 0.000000		SIZE A1	
				CAGE CODE 00779	
				DRAWING NO 206496	
				RESTRICTED TO -	
				CUSTOMER DRAWING	
				SCALE 20:1	
				SHEET 1 OF 1	
				REV G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206496-2](#)