


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
—	—		A2	REVISED PER ECO-15-014342		07OCT2015	RH

1 HARDWARE SUPPLIED WITH THREADED-BUSHING
PARTS ONLY: TE P/N 2213733-3 (NUT) X2
P/N 2213733-2 (LOCKING WASHER) X1



MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3,5-6	N/A	2-1,5-4
SCHEMATIC			

SWITCH FUNCTION

WITHOUT LOCKING RING

WITH STANDARD LOCKING RING

PANEL MOUNTING



P.C MOUNTING

LAYOUT FOR PN 2267077-2

SPECIFICATIONS

- MECHANICAL LIFE: 30,000 MAKE-AND-BREAK CYCLES.
- CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR BOTH SILVER AND GOLD PLATED CONTACTS.
- CONTACT RATING: GOLD PLATED: 0.4VA MAX @ 20 V MAX (AC OR DC)
- INSULATION RESISTANCE: 1,000 MΩ MIN.
- DIELECTRIC STRENGTH: 1,000 Vrms MIN.@SEA LEVEL.
- OPERATING TEMPERATURE: -30°C TO 85°C.




SILVER	ON-ON	SOLDER LUG	VERTICAL	2	2	TMD1T4B5M1QE	2267077-3
GOLD	ON-ON	PC THROUGH HOLE	VERTICAL	2	2	TMD1T4B5M2RE	2267077-2
GOLD	ON-ON	PC THROUGH HOLE	VERTICAL	1	2	TMS1T4B5M2RE	2267077-1
CONTACT MATERIAL	FUNCTION	TERMINATION	MOUNT ANGLE	POLES	THROWS	DESCRIPTIVE PN	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10JUL2014 NAGALAKSHMI K	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK 10JUL2014 HILL, RYAN					
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 10JUL2014 HILL, RYAN	NAME			
		0 PLC ± - 1 PLC ± 0.38[.015] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°	PRODUCT SPEC				
MATERIAL -		FINISH -	APPLICATION SPEC	SUBMINIATURE TOGGLE SWITCH			
			-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			WEIGHT -	A2	00779	C-2267077	-
CUSTOMER DRAWING				SCALE 3:1		SHEET 1 OF 3	REV A2

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—

MODEL NO.	POS.1	POS.2	POS.3
TMD	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING

P.C MOUNTING

LAYOUT FOR PN 2267077-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

NAGALAKSHMI K

10JUL2014

CHK

HILL, RYAN

10JUL2014

APVD

HILL, RYAN

10JUL2014

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.38[.015]

2 PLC ± 0.25[.010]

3 PLC ± -

4 PLC ± -

ANGLES ± 5°

MATERIAL

—

FINISH

—

TE Connectivity

NAME

SUBMINIATURE TOGGLE SWITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2267077

—

SCALE

SHEET

REV

3:1




2 OF 3

A2


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-

MODEL NO.	POS.1	POS.2	POS.3
TMD	ON	NONE	ON
TERM. COMM.	2-3,5-6		2-1,5-4
SCHEMATIC		N/A	

SWITCH FUNCTION





PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267077-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 10JUL2014		 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 10JUL2014							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HILL, RYAN 10JUL2014		NAME SUBMINIATURE TOGGLE SWITCH				
	0 PLC ± -		PRODUCT SPEC						
	1 PLC ± 0.38[.015]		—						
	2 PLC ± 0.25[.010]		APPLICATION SPEC						
	3 PLC ± -		—						
4 PLC ± -		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH		WEIGHT	A2 00779 C=2267077		—		
—		—		CUSTOMER DRAWING			SCALE 3:1	SHEET 3 of 3	REV A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TMD1T4B5M2RE](#)