

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REVISED

PER

ECO-14-014057

DATE

18FEB2015

DWN

NK

APVD

RH

Materials

No.	Component name	Base material	Finish
1	Housing	High Temp., UL 94V-0, green	
2	End terminal	silver clad copper alloy	5 microinches min. gold
3	Center terminal	copper alloy	5 microinches min. gold
4	Rocker contact	silver clad copper alloy	5 microinches min. gold
5	Actuator	Phenol resin, UL94 HB, black	
6	Plunger	stainless steel	
7	Spring	music wire	
8	Lever	brass	chrome or nickel
9	Retainer	Polyamide, UL94 HB, black	
10	Frame	cold rolled steel	zinc or nickel
11	Bushing	brass	100 microinches min. nickel over 10 microinches min. copper
12	Mounting nuts (2)	brass	200 microinches min. bright nickel
13	Locating ring	cold rolled steel	zinc or nickel
14	Internal tooth lockwasher	steel	zinc or nickel
15	Upper toggle cap	Aluminum	matte
16	Lower toggle cap	Aluminum	matte
17	Retaining pin	steel	

Specifications-see note 3

Current rating UL & CSA	6A @ 125 VAC (resistive)			
	3A @ 250 VAC (resistive)			
	4A @ 28 VDC (resistive)			
Termination resistance	20 milliohms max @ 2-4 VDC, 1A			
Insulation resistance	1,000 megohms min.			
Withstanding voltage	1,000 VAC			
Travel	24 +/-6 degrees			
Actuation force	.05 to 1.5 kgf			
Operating temperature	-20C to +85C			
Storage temperature	-40C to +85C			
Contact timing	break before make			
Terminal seal	epoxy or insert molded			
Durability	Parameter	2 Position	3 Position	Momentary
	mechanical (no load)	150,000	100,000	80,000
	250 VAC (3A resistive)	80,000	60,000	60,000
	125 VAC (6A resistive)	80,000	60,000	60,000
	28 VDC (4A resistive)	60,000	50,000	40,000

RECOMMENDED HOLE LAYOUT

TO PREVENT ROTATION

TO PREVENT ROTATION

PC BOARD LAYOUT

PC TERMINAL ONLY

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

NOT TO SCALE

Part Number	Alco Model	Poles	Throws	Function	Terminal				Comments
4-1437559-5	MTL406PA	2	3	ON ON ON	Wire lug	5-6, 11-12	5-3, 11-9	5-1, 11-7	note 7
4-1437559-4		4	2	ON ON	Wire lug	2-3, 5-6, 8-9, 11-12	---	2-1, 5-4, 8-7, 11-10	
4-1437559-3		3	2	ON OFF ON	Wire lug	2-3, 5-6, 8-9	Off	2-1, 5-4, 8-7	
4-1437559-2		3	2	ON ON	Wire lug	2-3, 5-6, 8-9	---	2-1, 5-4, 8-7	
4-1437559-1		2	2	(ON) OFF (ON)	Wire lug	2-3, 5-6	Off	2-1, 5-4	
4-1437559-0	MTL206PA	1	3	ON ON ON	Wire lug	5-6	5-3	5-1	note 6
3-1437559-9		2	2	ON OFF ON	Wire lug	2-3, 5-6	Off	2-1, 5-4	
3-1437559-8	MTL206NPC	2	2	ON ON	PC	2-3, 5-6	---	2-1, 5-4	
3-1437559-7		2	2	ON ON	Wire lug	2-3, 5-6	---	2-1, 5-4	
3-1437559-6	MTL106EUL	1	2	ON OFF ON	Wire lug	2-3	Off	2-1	
3-1437559-5		1	2	ON OFF ON	Wire lug	2-3	Off	2-1	
3-1437559-4		1	2	ON ON	Wire lug	2-3	---	2-1	

1

2

3

4

5

6

7

8

9

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± .

1 PLC ± .

2 PLC ± .

3 PLC ± .005

4 PLC ± .

ANGLES ± .

MATERIAL -

FINISH -

DWN M.BINNER

CHK M.ZITTO

APVD M.ZITTO

29DEC03

29DEC03

29DEC03

NAME

TOGGLE SWITCH,MTL SERIES

VERTICAL MOUNT

SIZE A1

CAGE CODE 00779

DRAWING NO 3-1437559-7

RESTRICTED TO

CUSTOMER DRAWING


SCALE 1:1

SHEET 1 OF 3


REV D5

4805 (3/11)


LOC	DIST	REVISIONS				
		REV	DATE	BY	APP'D	DESCRIPTION
AD	00	—	—	—	—	SEE SHEET 1




MTL-106      MTL-206



WIRE LUG TERMINAL







PC TERMINAL




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER 29DEC03	TE Connectivity	
		CHK M. ZITTO 29DEC03		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APP'D M. ZITTO 29DEC03	NAME TOGGLE SWITCH, MTL SERIES VERTICAL MOUNT	
		PRODUCT SPEC	—	
	0. PLC ± — 1. PLC ± — 2. PLC ± — 3. PLC ± .005 4. PLC ± — ANGLES ± —	APPLICATION SPEC	—	
		FINISH	—	
MATERIAL	—	WEIGHT	—	
CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 3	REV D5

LOC		DIST		REVISIONS			
AD	00	FP	LTR	DESCRIPTION		DATE	DWN
		-	-	SEE SHEET 1		-	-






COUNTRY OF ORGIN  
STAMPED HERE  
EXISTING  
SWITCHES ONLY



WIRE LUG TERMINAL

PC TERMINAL



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: M. BINNER 29DEC03	 TE Connectivity			
DIMENSIONS: INCHES		CHK: M. ZITTO 29DEC03				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TOGGLE SWITCH, MTL SERIES VERTICAL MOUNT —			
	0 PLC	± —		PRODUCT SPEC  APPLICATION SPEC  WEIGHT — —		
	1 PLC	± —				
	2 PLC	± —				
	3 PLC	± .005				
4 PLC	± —	SIZE A1	CAGE CODE 00779	DRAWING NO. C3-1437559-7	RESTRICTED TO —	
ANGLES	± —					
MATERIAL —	FINISH —	CUSTOMER DRAWING		SCALE 1:1	SHEET 3 OF 3	REV D5

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MTL206P](#)