


REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	G2	REVISED PER ECO-16-006286	17JUN2016	NK	DR




AMP WIRE RANGE	 E13288 Listed
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED
 LR7189 Certified	 MILITARY P/N AND CLASS
2/0 AWG SOLID OR STRANDED	MS 20659-120 CLASS 2

-  STAMP AMP 2/0W* APPROX AS SHOWN
-  TIN PL 0.00254[.000100] MIN EXT THK PER ASTM B-545
-  BRIGHT TIN LEAD PL 0.00254[.000100] MIN THK PER ASTM B-545
-  NICKEL PLATE 0.00762 [.000300] MIN EXT. THK PER SAE AMS QQ-N-290

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm ² [119,500-150,500] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
FOR ORDER ENTRY	1-800-526-5142	



170°C[338°F]	50	LOOSE PIECE		2-321871-2
343°C[650°F]	50	LOOSE PIECE		321871-2
170°C[338°F]	50	LOOSE PIECE		321871
MAX OPERATIVE TEMPERATURE	QTY	PACKAGE TYPE	FINISH	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 1/14/94	 TE Connectivity	
		CHK AJ KAUFMAN 1/19/94		
		APVD JL MECKLEY 1/19/94	NAME TERMINAL, RING TONGUE, SOLISTRAND	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ± - ANGLES	SIZE A2	
MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH SEE TABLE		
		WEIGHT	DRAWING NO G-321871	
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 1
			REV G2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[321871-2](#)