




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECO-16-002001	25MAY2016	LN	RS



SAME AS VIEW X EXCEPT AS SHOWN

- 1 SILVER PLATE PER QQ-S-365, 5.08μm[.000200] MIN THK
- 2 GOLD PLATE PER MIL-G-45204, 1.27μm[.000050] MIN THK
- 3 NICKEL PLATE PER QQ-N-290, 2.54μm[.000100] MIN THK
- 4 PASSIVATE PER QQ-P-35
- 5 5/8-24 UNEF-2B
- 6 7/16-28 UNEF-2B
- 7 1/4-36 UNS-2B

	X	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	9-332004-1
	Y	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	9-332004-0
	X	5	3.18 [.125]	19.05±0.38[.750±.015]	3	BRASS PER QQ-B-626	2-332004-3
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	3	BRASS PER QQ-B-626	2-332004-2
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	4	SST PER ASTM-A-582	2-332004-0
OBSOLETE	X	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	1-332004-9
	Y	5	3.18 [.125]	19.05±0.38[.750±.015]	3	BRASS PER QQ-B-626	1-332004-7
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	2	SST PER ASTM-A-582	1-332004-5
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	-	SST PER ASTM-A-582	1-332004-4
OBSOLETE	Y	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	1-332004-0
	VIEW	THREADS	B	A	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SNEED 5-18-93		 TE Connectivity	
		CHK J. DUNBAR 5-18-93			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD M. SNEED 5-18-93		JAM NUT	
		PRODUCT SPEC		—	
		APPLICATION SPEC		—	
		—		SIZE	
		—		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
SEE TABLE		SEE TABLE		RESTRICTED TO	
		WEIGHT 0.000000		A2 00779 C=332004	
		CUSTOMER DRAWING		SCALE 4:1	
				SHEET 1 of 1	
				REV D1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-332004-5](#)