

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

ATLANTIC VERSION
TERMINATOR
INTERFACE ADAPTER

PART
NUMBER

REVISION

DESCRIPTION

FEED TYPE

CONVERT TO

PART NUMBERS REQUIRED

2150244-1

A

FINE CRIMP HEIGHT ADJUST

MECHANICAL

PNEUMATIC FEED

SERVO LATCH PLATE

SMART APPLICATOR

2119950-1

2119951-1

2161326-1

2119792-1

1901697-1

-

-

-

-

2119641-1

-

-

-

2063440-1

-

2150244-2

A

FINE CRIMP HEIGHT ADJUST

PNEUMATIC

MECHANICAL FEED

SERVO LATCH PLATE

SMART APPLICATOR

2119949-1

2119951-1

2161326-1

2063961-1

1901697-1

-

5-18022-5

8-2150244-5

8-2150244-4

2119653-1

-

-

-

2168400-7 (QUANTITY 2)

-

2150244-5

A

FINE CRIMP HEIGHT ADJUST

SERVO
LATCH PLATE⁴

MECHANICAL FEED

PNEUMATIC FEED

2119949-1

2119950-1

2119792-1

2063961-1

-

-

5-18022-5

-

-

2119653-1

-

-

-

2063440-1

-

2150244-6

A

NON-CRIMP HEIGHT ADJUST

SERVO
LATCH PLATE⁴¹²

-

-

-

-

-

-

-

-

-

-

-

-

2150244-7

A

FINE CRIMP HEIGHT ADJUST

NONE

-

-

-

-

-

-

-

-

-

-

-

-

7-2150244-7

A

CRIMP TOOLING KIT

-

-

-

-

-

-

-

-

-

-

-

-

-

APPLICATOR DATA

CRIMP

SIZE

TYPE

WIRE

2.29 mm [.090]

F

INSUL

3.56 mm [.140]

F

APPL INSTRUCTIONS

408-10390

TERMINAL DATA: TE TERMINAL

TE CRIMP SPECIFICATION

TERMINAL NAME: .250 SERIES FASTON TAB

WIRE STRIP LENGTH

INSULATION DIAMETER RANGE

4.32-5.10 mm [.170-.201 IN]

Ø2.00-3.00 mm [.079-.118 IN]

TERMINAL APPLICATION SPECIFICATION

114-20021

-

-

-

-

-

-

TERMINALS APPLIED

¹³

TE TERMINAL

TE TERMINAL

TE TERMINAL

TE TERMINAL

626377-1

626377-2

626377-3

626377-4

WIRE SIZE

CRIMP HEIGHT mm [INCH]

CRIMP HEIGHT REFERENCE SETTING⁹

1.00mm2

1.40+/-0.000 [.055+/- .000]

11.6

0.75mm2

1.32+/-0.000 [.052+/- .000]

12.5

0.50mm2

1.22+/-0.000 [.048+/- .000]

13.4

¹ RECOMMENDED SPARE PARTS

² GREASE BEARING SURFACES LIGHTLY

3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

⁴ APPLICATOR SPECIFIC DATA TO BE ENTERED INTO BLANK MEMORY CHIP AT ASSEMBLY. SEE BELOW FOR PART NUMBER:
MECHANICAL FEED WITH "SMART APPLICATOR" CONVERSION: 8-2150244-4
PNEUMATIC FEED WITH "SMART APPLICATOR" CONVERSION: 8-2150244-4
SERVO FEED WITH "FINE CRIMP HEIGHT ADJUST": 8-2150244-5
SERVO FEED WITH "NON-CRIMP HEIGHT ADJUST": 8-2150244-6

5. ADJUSTMENT OF THE STRIPPER MAY BE REQUIRED WHEN MOVING THE APPLICATOR BETWEEN BENCH AND LEADMAKER APPLICATIONS.

⁶ APPLY PART NUMBER 1-23419-5 LOCTITE TO THREADS OF ITEM 50.

⁷ GREASE THREADS, GROOVE AND O-RING ON ITEMS 35 & 252.

⁸ MAGNET, ITEM 166 MUST BE ORIENTED CORRECTLY IN ORDER TO PROPERLY ACTUATE THE COUNTER.

⁹ CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.

¹⁰ SPARE FEED CAM STORAGE LOCATION REFER TO INSTRUCTION SHEET FOR ADDITIONAL INFORMATION.

¹¹ THE RECOMMENDED SET-UP FOR END FEED APPLICATORS IS POST-FEED WITH ITEM 2119653-1. THE APPLICATOR CAN BE CONFIGURED FOR PRE-FEED WITH ITEM 2119652-1 BUT MAY ENCOUNTER PROBLEMS WITH SOME APPLICATIONS. FEED ISSUES OR TERMINAL JAMMING MAY OCCUR IN THE PRE-FEED CONFIGURATION.

¹² WHEN ASSEMBLING -6 NON-CRIMP HEIGHT ADJUST APPLICATOR USE SHIM PACK 2119957-2 TO ALIGN APPLICATOR'S MAXIMUM WIRE CRIMP HEIGHT AT NORMAL TERMINATOR SHUT HEIGHT

¹³ FEED OFF INSULATION BARREL.

6

5

4

3

2

1

LOC

DIST

REV

SET UP GAUGE

2119599-2

A

66

REVISIONS

DESCRIPTION

DATE

OWN

APVD

1

1

1

1

1

1

2119082-9

CAM, SNAIL, INSULATION ADJUSTMENT

244

1

1

1

1

1

1

2079764-1

WASHER, WAVE SPRING, CREST-TO-CREST

243

1

1

1

1

1

1

2119083-1

RETAINER, INSULATION DIAL

242

2

2

-

-

-

-

2168400-7

SHCS, LOW HEAD, RoHS, M5 X 10

240

-

-

-

-

-

1

2119580-1

MECHANICAL FEED ASSEMBLY

239

-

-

-

-

-

-

2063440-1

AIR FEED MODULE

238

-

1

1

-

-

-

2119740-2

TAG, IDENTIFICATION

213

-

REF

REF

-

-

-

1901697-1

FEED FINGER ASSEMBLY, EF

183

1

1

1

1

1

1

6-993111-6

PIN, SLOTTED SPRING 3.0 X 14.0

177

1

1

1

1

1

1

8-22280-7

SPRING, COMPRESSION

176

1

1

1

1

1

1

1752353-2

GUIDE PIN, HOLDDOWN

175

1

1

1

1

1

1

1901680-2

GUIDE PIN, HOLDDOWN

174

-

-

-

2

-

-

21045-3

RING, RETAIN, EXTERN, 3/16 CRESCENT

172

1

1

1

1

1

1

994969-1

MAGNET, RARE EARTH HIGH ENERGY

166

-

REF

REF

REF

REF

REF

994970-2

COUNTER, MAGNETIC

164

-

-

-

-

1

-

240638-1

SPRING, FEED FINGER

163

-

-

-

-

1

-

3-23627-7

PIN, RETAIN, GRVD, 3/16 X .854

137

-

REF

REF

-

-

-

SEE NOTE 4

MEMORY CHIP, PROGRAMMED

135

-

1

1

-

-

-

1633743-1

SERVO FEED LATCH ASM

133

1

1

1

1

1

1

455888-4

SPACER, CRIMPER

82

1

1

1

1

1

1

2119791-5

DEPRESSOR, WIRE

73

1

1

1

1

1

1

2119956-2

DOCUMENTATION PACKAGE

71

2

2

2

2

2

2

2-18032-2

SCR, SET, FLT POINT M3 X 10.0

70

1

1

1

1

1

1

2119943-1

WASHER, SPACER

69

1

-

-

1

1

1

2119740-1

TAG, IDENTIFICATION

67

2

2

2

2

2

2

2168078-1

SCREW, DRIVE, RH, RoHS

66

1

1

1

1

1

1

1901681-1

HOLDDOWN, TERMINAL

65

1

-

1

1

1

1

2119793-1

LIMITER, ADJUSTMENT BOLT

63

3

-

3

3

3

3

992763-5

SCR, SET, SOC, CONE POINT, M3 x 4.0

62

1

1

1

1

1

1

2079383-4

SCR, BHSC, RoHS (M4 X 8)

60

-

-

-

-

1

-

5-18022-5

SCR, HEX HD CAP, M4 X 6.0

59

-

-

-

-

-

1

2063961-1

FEED FINGER

58

-

4

4

4

4

4

2168400-4

SHCS, LOW HEAD, RoHS, M4 X 8

57

2

2

2

2

2

2

2168083-3

SCR, SKT HD CAP, RoHS, M4 X 12.0

56

2

2

2

2

2

2

5018030-2

NUT, HEX, REG, RoHS, M4

55

2

2

2

2

2

2

5018030-1

NUT, HEX, REG, RoHS, M3

54

2

2

2

2

2

2

986965-8

NUT, LOCK, HEX, TORQUE (M4)

53

1

1

1

1

1

1

1-5018030-0

NUT, HEX, REG, RoHS, M3.5

52

-

-

-

-

1

-

2119792-1

PAWL, EF, AIR

51

1

1

1

1

1

1

1752354-5

STANDOFF, HOLD-DOWN

50

-

-

-

-

1

2

18023-9

SCR, SKT HD CAP M4 X 6.0

49

-

-

-

-

-

1

2119653-1

FEED CAM, POST FEED

47

1

1

1

1

1

1

2119655-5

APPLICATOR BASIC ASSEMBLY, EF

46

1

-

1

1

1

1

2119369-1

RAM, AMP STYLE, END FEED

44

1

1

1

1

1

1

2079383-7

SCR, BHSC, RoHS (M8 X 25)

41

1

-

1

1

1

1

2119645-1

DISC, NUMBERED FA WIRE ADJUSTMENT

40

1

-

1

1

1

1

2119957-1

APPLICATOR SHIM PACK

39

1

1

1

1

1

1

2119644-2

RAM WASHER, PRECISION

38

1

1

1

1

1

1

2119085-1

FA HEAD, ATLANTIC STYLE

37

1

-

1

1

1

1

2119092-1

BOLT, ADJUSTMENT

35

8

8

8

8

8

8

1-18028-2

WASHER, FLAT, REG M4

33

2

2

2

2

2

2

2168083-9

SCR, SKT HD CAP, RoHS, M4 X 20

31

2

2

2

2

2

2

1-2168083-0

SCR, SKT HD CAP, RoHS, M4 X 10

29

1

1

1

1

1

1

240639-1

STRIPPER (MACHINING)

27

2

2

2

2

2

2

1320906-1

STUD, THREADED

25

1

1

1

1

1

1

1-1752371-2

PLATE, STRIP GUIDE

24

2

2

2

2

2

2

2-22281-3

SPRING, COMPRESSION

22

1

1

1

1

1

1

1752373-1

DRAG

20

1

1

1

1

1

1

1-1901696-8

STRIP GUIDE, REAR

19

1

1

1

1

1

1

1-1901695-8

STRIP GUIDE, FRONT

18

4

4

4

4

4

4

1-2079383-1

SCR, BHSC, RoHS (M6 X 12)

17

1

1

1

1

1

1

8-240641-4

SPACER

16

1

1

1

1

1

1

1752360-1

SPACER, HOLD-DOWN

13

1

1

1

1

1

1

240644-5

PLATE, REAR SHEAR

11

-

-

-

-

-

-

-

-

-

-

-

-

1

1

1

1

1

1

3-690482-4

PLATE, FRONT SHEAR

9

1

1

1

1

1

1

1803000-3

ANVIL, COMBINATION, END FEED

8

1

1

1

1

1

1

690474-6

BLADE, SLUG

7

1

1

1

1

1

1

1-240641-8

SPACER

5

1

1

1

1

1

1

2-238009-3

BLOCK, FL CRIMPER SPACER

4

1

1

1

1

1

1

2-2119582-4

CRIMPER, INSULATION F PREMIUM

3

1

1

1

1

1

1

455888-1

SPACER, CRIMPER

2

1

1

1

1

1

1

4-456406-7

CRIMPER, WIRE PREMIUM

1

-

7

-

6

-

5

-

2

-

1

2119082-9

CAM, SNAIL, INSULATION ADJUSTMENT

244

-

1

1

1

1

1

2079764-1

WASHER, WAVE SPRING, CREST-TO-CREST

243

1

1

1

1

1

1

2119083-1

RETAINER, INSULATION DIAL

242

2

2

-

-

-

-

2168400-7

SHCS, LOW HEAD, RoHS, M5 X 10

240

-

-

-

-

-

1

2119580-1

MECHANICAL FEED ASSEMBLY

239

-

-

-

-

-

-

2063440-1

AIR FEED MODULE

238

-

1

1

-

-

-

2119740-2

TAG, IDENTIFICATION

213

-

REF

REF

-

-

-

1901697-1

FEED FINGER ASSEMBLY, EF

183

1

1

1

1

1

1

6-993111-6

PIN, SLOTTED SPRING 3.0 X 14.0

177

1

1

1

1

1

1

8-22280-7

SPRING, COMPRESSION

176

1

1

1

1

1

1

1752353-2

GUIDE PIN, HOLDDOWN

175

1

1

1

1

1

1

1901680-2

GUIDE PIN, HOLDDOWN

174

-

-

-

2

-

-

21045-3

RING, RETAIN, EXTERN, 3/16 CRESCENT

172

1

1

1

1

1

1

994969-1

MAGNET, RARE EARTH HIGH ENERGY

166

-

REF

REF

REF

REF

REF

994970-2

COUNTER, MAGNETIC

164

-

-

-

-

1

-

240638-1

SPRING, FEED FINGER

163

-

-

-

-

1

-

3-23627-7

PIN, RETAIN, GRVD, 3/16 X .854

137

-

REF

REF

-

-

-

SEE NOTE 4

MEMORY CHIP, PROGRAMMED

135

-

1

1

-

-

-

1633743-1

SERVO FEED LATCH ASM

133

1

1

1

1

1

1

455888-4

SPACER, CRIMPER

82

1

1

1

1

1

1

2119791-5

DEPRESSOR, WIRE

73

1

1

1

1

1

1

2119956-2

DOCUMENTATION PACKAGE

71

2

2

2

2

2

2

2-18032-2

SCR, SET, FLT POINT M3 X 10.0

70

1

1

1

1

1

1

2119943-1

WASHER, SPACER

69

1

-

-

1

1

1

2119740-1

TAG, IDENTIFICATION

67

2

2

2

2

2

2

2168078-1

SCREW, DRIVE, RH, RoHS

66

1

1

1

1

1

1

1901681-1

HOLDDOWN, TERMINAL

65

1

-

1

1

1

1

2119793-1

LIMITER, ADJUSTMENT BOLT

63

3

-

3

3

3

3

992763-5

SCR, SET, SOC, CONE POINT, M3 x 4.0

62

1

1

1

1

1

1

2079383-4

SCR, BHSC, RoHS (M4 X 8)

60

-

-

-

-

1

-

5-18022-5

SCR, HEX HD CAP, M4 X 6.0

59

-

-

-

-

-

1

2063961-1

FEED FINGER

58

-

4

4

4

4

4

2168400-4

SHCS, LOW HEAD, RoHS, M4 X 8

57

2

2

2

2

2

2

2168083-3

SCR, SKT HD CAP, RoHS, M4 X 12.0

56

2

2

2

2

2

2

5018030-2

NUT, HEX, REG, RoHS, M4

55

2

2

2

2

2

2

5018030-1

NUT, HEX, REG, RoHS, M3

54

2

2

2

2

2

2

986965-8

NUT, LOCK, HEX, TORQUE (M4)

53

1

1

1

1

1

1

1-5018030-0

NUT, HEX, REG, RoHS, M3.5

52

-

-

-

-

1

-

2119792-1

PAWL, EF, AIR

51

1

1

1

1

1

1

1752354-5

STANDOFF, HOLD-DOWN

50

-

-

-

-

1

2

18023-9

SCR, SKT HD CAP M4 X

DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009



C

B


A

8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION 20	
© COPYRIGHT 20		BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.	


LOC		DIST		REVISONS			
A	66	P	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-




FEED TYPE
MECHANICAL





PNEUMATIC



SERVO
LATCH PLATE




CAM POSITIONS




ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)


THIS DRAWING IS UNPUBLISHED. IT IS CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE KEPT IN CONFIDENTIALITY AND NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. ANY UNAUTHORIZED REPRODUCTION OR TRANSMISSION OF THIS DRAWING IS PROHIBITED. ANY VIOLATION OF THIS NOTICE SHALL BE CONSIDERED A VIOLATION OF THE APPLICABLE LAWS AND REGULATIONS. ANY VIOLATION OF THIS NOTICE SHALL BE CONSIDERED A VIOLATION OF THE APPLICABLE LAWS AND REGULATIONS. ANY VIOLATION OF THIS NOTICE SHALL BE CONSIDERED A VIOLATION OF THE APPLICABLE LAWS AND REGULATIONS.		DWN HOFFNER 11JAN2012	TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK T.ELBIN 11JAN2012	NAME Ocean End Feed Applicator	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.5 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.001 ANGLES ±.1		APVD T.ELBIN 11JAN2012	PRODUCT SPEC	
MATERIAL			APPLICATION SPEC	
			WEIGHT	
			CUSTOMER ACCESSIBLE PRODUCTION DRAWING	
			SCALE 1:1 SHEET 2 OF 4 REV A	




HOLDDOWN SET-UP



CAM POSITIONS



MECHANICAL POST FEED




AIR FEED


PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

LOC		DIST		REVISES			
A	66	P	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-


FEED TYPE
MECHANICAL



PNEUMATIC



SERVO
LATCH PLATE



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION AND IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION. IT IS THE RESPONSIBILITY OF THE USER TO CONTACT TYCO ELECTRONICS CORPORATION FOR THE LATEST REVISION.				DWN HOFFNER 10JAN2012		TE Connectivity Harrisburg, PA 17105-3608	
C44 T. ELBIN 11JAN2012				NAME		Ocean End Feed Applicator	
APVD T. ELBIN 11JAN2012				PRODUCT SPEC		SIZE A1	
				APPLICATION SPEC		CAGE CODE 00779	
				WEIGHT		DRAWING NO C-2150244	
				CUSTOMER ACCESSIBLE PRODUCTION DRAWING		RESTRICTED TO	
				SCALE 1:1		SHEET 4 OF 4	
						REV A	

SHEETS 1 & 2 ARE NOT REQUIRED FOR PACIFIC VERSION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2150244-2](#)