

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2017

© COPYRIGHT 2017

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

ATLANTIC VERSION TERMINATOR INTERFACE ADAPTER

PART NUMBER


REVISION

DESCRIPTION

FEED TYPE

CONVERT TO

PART NUMBERS REQUIRED



2150800-1

A

FINE CRIMP HEIGHT ADJUST

MECHANICAL

PNEUMATIC FEED

SERVO LATCH PLATE

SMART APPLICATOR

2119950-1

2119951-1

2161326-1

1-2119792-4

1901697-1

-

-

-

-

2119641-1

-

-

-

2063440-1

2168400-7 (QUANTITY 2)

2150800-2

A

FINE CRIMP HEIGHT ADJUST

PNEUMATIC

MECHANICAL FEED

SERVO LATCH PLATE

SMART APPLICATOR

2119949-1

2119951-1

2161326-1

2063961-7

1901697-1

8-2150800-5

5-18022-5

-

-

2119653-1

-

-

-

2168400-7 (QUANTITY 2)

-

2150800-5

A

FINE CRIMP HEIGHT ADJUST

SERVO LATCH PLATE

MECHANICAL FEED

PNEUMATIC FEED

2119949-1

2119950-1

2063961-7

5-18022-5

1-2119792-4

-

2119653-1

-

-

-

-

2063440-1

2150800-6

A

NON-CRIMP HEIGHT ADJUST

SERVO LATCH PLATE

-

-

-

-

-

-

-

-

-

-

-

-

2150800-7

A

FINE CRIMP HEIGHT ADJUST

NONE

-

-

-

-

-

-

-

-

-

-

-

-

7-2150800-7

A

CRIMP TOOLING KIT

-

-

-

-

-

-

-

-

-

-

APPLICATOR DATA

CRIMP

SIZE

TYPE

WIRE

2.10 mm [.083]

F

INSUL

2.30 mm [.091]

F

APPL INSTRUCTIONS

408-10390



TERMINAL DATA: STOCKO TERMINAL STOCKO CRIMP SPECIFICATION

TERMINAL NAME: CONNECTOR TERMINAL

WIRE STRIP LENGTH

INSULATION DIAMETER RANGE

4.80-5.80 mm [.189-.228 IN]

Ø0.90-1.80 mm [.035-.071 IN]

TERMINAL APPLICATION SPECIFICATION

F 071-2 Rev 12/12/2007

-

-

-

TERMINALS APPLIED

TE TERMINAL

STOCKO TERMINAL

TE TERMINAL


STOCKO TERMINAL

2303750-1

RSB 8115 F6.3-0.2

WIRE SIZE





CRIMP HEIGHT mm [INCH]



CRIMP HEIGHT REFERENCE SETTING



22 AWG OR 0.34mm2

1.28+/-0.02 [.050+/- .001]

8.2

24 AWG OR 0.22mm2

1.22+/-0.02 [.048+/- .001]

9.0

26 AWG OR 0.12mm2

1.18+/-0.02 [.046+/- .001]

9.5

1

RECOMMENDED SPARE PARTS

2

GREASE BEARING SURFACES LIGHTLY

3

LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

4

APPLICATOR SPECIFIC DATA TO BE ENTERED INTO BLANK MEMORY CHIP AT ASSEMBLY. SEE BELOW FOR PART NUMBER:
MECHANICAL FEED WITH "SMART APPLICATOR" CONVERSION: 8-2150800-4
PNEUMATIC FEED WITH "SMART APPLICATOR" CONVERSION: 8-2150800-4
SERVO FEED WITH "FINE CRIMP HEIGHT ADJUST": 8-2150800-5
SERVO FEED WITH "NON-CRIMP HEIGHT ADJUST": 8-2150800-6

5

ADJUSTMENT OF THE STRIPPER MAY BE REQUIRED WHEN MOVING THE APPLICATOR BETWEEN BENCH AND LEADMAKER APPLICATIONS.

6

APPLY PART NUMBER 1-23419-5 LOCTITE TO THREADS OF ITEMS 62 & 180.
APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.
FOR -6 ONLY APPLY PART NUMBER 1-23419-5 LOCTITE TO THREADS OF ITEMS 37 & 180.

7

GREASE THREADS, GROOVE AND O-RING ON ITEMS 35 & 252.

8

MAGNET, ITEM 166 MUST BE ORIENTED CORRECTLY IN ORDER TO PROPERLY ACTUATE THE COUNTER.

9

CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.

10

SPARE FEED CAM STORAGE LOCATION REFER TO INSTRUCTION SHEET FOR ADDITIONAL INFORMATION.

11

THE RECOMMENDED SET-UP FOR END FEED APPLICATORS IS POST-FEED WITH ITEM 2119653-1. THE APPLICATOR CAN BE CONFIGURED FOR PRE-FEED WITH ITEM 2119652-1 BUT MAY ENCOUNTER PROBLEMS WITH SOME APPLICATIONS. FEED ISSUES OR TERMINAL JAMMING MAY OCCUR IN THE PRE-FEED CONFIGURATION.

12

WHEN ASSEMBLING -6 NON-CRIMP HEIGHT ADJUST APPLICATOR USE SHIM PACK 2119957-2 TO ALIGN APPLICATOR'S MAXIMUM WIRE CRIMP HEIGHT AT NORMAL TERMINATOR SHUT HEIGHT

13

TERMINAL LUBRICANT IS RECOMMENDED.

14

FEED FROM END OF TERMINAL BODY.

6

1

1

1

1

1

2119083-1

RETAINER, INSULATION DIAL

242

6

-

2

2

-

-

2168400-7

SHCS, LOW HEAD, RoHS, M5 X 10

240

6

-

-

-

-

1

2119580-1

MECHANICAL FEED ASSEMBLY

239

6

-

-

-

-

1

2063440-1

AIR FEED MODULE

238

6

-

1

1

-

-

2119740-2

TAG, IDENTIFICATION

213

6

-

2

2

2

2

2168083-1

SCR, SKT HD CAP, RoHS, M3 X 8.0

191

6

-

-

REF

REF

-

-

1901697-1

FEED FINGER ASSEMBLY, EF

183

6

-

1

1

1

1

1

1-1976055-1

STANDOFF, HOLD-DOWN

180

6

-

1

1

1

1

1

6-993111-6

PIN, SLOTTED SPRING 3.0 X 14.0

177

6

-

1

1

1

1

1

8-22280-7

SPRING, COMPRESSION

176

6

-

1

1

1

1

1

1752353-2

GUIDE PIN, HOLDDOWN

175

6

-

1

1

1

1

1

1901680-2

GUIDE PIN, HOLDDOWN

174

6

-

-

-

2

-

21045-3

RING, RETAIN, EXTERN, 3/16 CRESCENT

172

6

-

1

1

1

1

1

994969-1

MAGNET, RARE EARTH HIGH ENERGY

166

6

-

REF

REF

REF

REF

REF

994970-2

COUNTER, MAGNETIC

164

6

-

-

-

-

1

-

240638-1

SPRING, FEED FINGER

163

6

-

-

-

-

1

-

3-23627-7

PIN, RETAIN, GRVD, 3/16 X .854

137

6

-

-

REF

REF

-

-

SEE NOTE 4

MEMORY CHIP, PROGRAMMED

135

6

-

-

1

1

-

-

1633743-1

SERVO FEED LATCH ASM

133

6

-

1

1

1

1

1

2119955-2

ASSY, LUBRICATOR, END FEED

84

6

-

1

1

1

1

1

455888-7

SPACER, CRIMPER

82

6

-

1

1

1

1

1

2119791-5

DEPRESSOR, WIRE

73

6

-

1

1

1

1

1

2119956-2

DOCUMENTATION PACKAGE

71

6

-

2

2

2

2

2

2-18032-2

SCR, SET, FLT POINT M3 X 10.0

70

6

-

1

-

-

1

1

2119740-1

TAG, IDENTIFICATION

67

6

-

2

2

2

2

2

2168078-1

SCREW, DRIVE, RH, RoHS, 2 x .188

66

6

-

1

1

1

1

1

1901681-5

HOLDDOWN, TERMINAL

65

6

-

1

-

1

1

1

2119793-1

LIMITER, ADJUSTMENT BOLT

63

6

-

3

-

3

3

3

992763-5

SCR, SET, SOC, CONE POINT, M3 x 4.0

62

6

-

1

1

1

1

1

2079383-4

SCR, BHSC, RoHS (M4 X 8)

60

6

-

-

-

-

-

1

5-18022-5

SCR, HEX HD CAP, M4 X 6.0

59

6

-

-

-

-

-

1

2063961-7

FEED FINGER

58

6

-

4

4

4

4

4

2168400-4

SHCS, LOW HEAD, RoHS, M4 X 8

57

6

-

2

2

2

2

2

1-2168083-0

SCR, SKT HD CAP, RoHS, M4 X 10

56

6

-

2

2

2

2

2

5018030-1

NUT, HEX, REG, RoHS, M3

54

6

-

2

2

2

2

2

986965-8

NUT, LOCK, HEX, TORQUE (M4)

53

6

-

1

1

1

1

1

1-5018030-0

NUT, HEX, REG, RoHS, M3.5

52

6

-

-

-

-

1

-

1-2119792-4

PAWL, EF, AIR

51

6

-

-

-

-

1

2

18023-9

SCR, SKT HD CAP M4 X 6.0

49

6

-

-

-

-

-

1

2119652-1

FEED CAM, PRE FEED

48

6

-

-

-

-

-

1

2119653-1

FEED CAM, POST FEED

47

6

-

1

1

1

1

1

2119655-5

APPLICATOR BASIC ASSEMBLY, EF

46

6

-

1

-

1

1

1

2119369-1

RAM, AMP STYLE, END FEED

44

6

-

1

1

1

1

1

2079383-7

SCR, BHSC, RoHS (M8 X 25)

41

6

-

1

-

1

1

1

2119645-1

DISC, NUMBERED FA WIRE ADJUSTMENT

40

6

-

1

-

1

1

1

2119957-1

APPLICATOR SHIM PACK

39

6

-

1

1

1

1

1

1-2119644-2

RAM WASHER, PRECISION

38

6

-

1

1

1

1

1

2119085-1

FA HEAD, ATLANTIC STYLE

37

6

-

1

-

1

1

1

2119092-1

BOLT, ADJUSTMENT

35

6

-

8

8

8

8

8

1-18028-2

WASHER, FLAT, REG M4

33

6

-

2

2

2

2

2

2168083-9

SCR, SKT HD CAP, RoHS, M4 X 20

31

6

-

2

2

2

2

2

2168083-2

SCR, SKT HD CAP, RoHS, M4 X 8.0

29

6

-

1

1

1

1

1

240639-1

STRIPPER (MACHINING)

27

6

-

2

2

2

2

2

1-2168083-5

SCR, SKT HD CAP, RoHS, M4 X 30

25

6

-

1

1

1

1

1

1-1752371-6

PLATE, STRIP GUIDE

24

6

-

2

2

2

2

2

22281-8

SPRING, COMPRESSION

22

6

-

1

1

1

1

1

1633168-1

ARM, STOCK DRAG

21

6

-

1

1

1

1

1

2-464452-1

DRAG, STOCK

20

6

-

1

1

1

1

1

1803152-2

STRIP GUIDE, REAR

19

6

-

1

1

1

1

1

1803151-2

STRIP GUIDE, FRONT

18

6

-

4

4

4

4

4

1-2079383-1

SCR, BHSC, RoHS (M6 X 12)

17

6

-

1

1

1

1

1

1752360-1

SPACER, HOLD-DOWN

13

6

-

1

1

1

1

1

1-240644-7

PLATE, REAR SHEAR

11

6

-

-

-

-

-

-

-

-

-

10

6

-

1

1

1

1

1

5-690495-3

PLATE, FRONT SHEAR

9

6

1

1

1

1

1

1

3-1803257-1

ANVIL, COMBINATION, END FEED

8

6

-

1

1

1

1

1

2212706-2

BLADE, SLUG

7

6

-

-

-

-

-

-

-

-

-

6

6

-

1

1

1

1

1

6-240641-9

SPACER

5

6

-

1

1

1

1

1

1-238009-0

BLOCK, FL CRIMPER SPACER

4

6

1

1

1

1

1

1

3-1803223-1

CRIMPER, INSULATION F PREMIUM

3

6

-

1

1

1

1

1

455888-6

SPACER, CRIMPER

2

6

1

1

1

1

1

1

9-1803241-9

CRIMPER, WIRE F

1

6

-

7

-

7

-

6

-

5

-

2

-

1

PART NO

DESCRIPTION

ITEM NO

ATLANTIC VERSION

Shown on sheets 1 of 4 & 2 of 4

(Pacific version shown on sheets 3 of 4 & 4 of 4)

SET UP GAUGE

LOC

DIST

2119599-2

A

66

P

LYR

DESCRIPTION

DATE

OWN

APVD

A

RELEASED

09JUN2017

LG

TE

6

1

1

1

1

1

2119083-1

RETAINER, INSULATION DIAL

242

6

-

2

2

-

-

2168400-7

SHCS, LOW HEAD, RoHS, M5 X 10

240

6

-

-

-

-

1

2119580-1

MECHANICAL FEED ASSEMBLY

239

6

-

-

-

-

1

2063440-1

AIR FEED MODULE

238

6

-

1

1

-

-

2119740-2

TAG, IDENTIFICATION

213

6

-

2

2

2

2

2168083-1

SCR, SKT HD CAP, RoHS, M3 X 8.0

191

6

-

-

REF

REF

-

-

1901697-1

FEED FINGER ASSEMBLY, EF

183

6

-

1

1

1

1

1

1-1976055-1

STANDOFF, HOLD-DOWN

180

6

-

1

1

1

1

1

6-993111-6

PIN, SLOTTED SPRING 3.0 X 14.0

177

6

-

1

1

1

1

1

8-22280-7

SPRING, COMPRESSION

176

6

-

1

1

1

1

1

1752353-2

GUIDE PIN, HOLDDOWN

175

6

-

1

1

1

1

1

1901680-2

GUIDE PIN, HOLDDOWN

174

6

-

-

-

2

-

21045-3

RING, RETAIN, EXTERN, 3/16 CRESCENT

172

6

-

1

1

1

1

1

994969-1

MAGNET, RARE EARTH HIGH ENERGY

166

6

-

REF

REF

REF

REF

REF

994970-2

COUNTER, MAGNETIC

164

6

-

-

-

-

1

-

240638-1

SPRING, FEED FINGER

163

6

-

-

-

-

1

-

3-23627-7

PIN, RETAIN, GRVD, 3/16 X .854

137

6

-

-

REF

REF

-

-

SEE NOTE 4

MEMORY CHIP, PROGRAMMED

135

6

-

-

1

1

-

-

1633743-1

SERVO FEED LATCH ASM

133

6

-

1

1

1

1

1

2119955-2

ASSY, LUBRICATOR, END FEED

84

6

-

1

1

1

1

1

455888-7

SPACER, CRIMPER

82

6

-

1

1

1

1

1

2119791-5

DEPRESSOR, WIRE

73

6

-

1

1

1

1

1

2119956-2

DOCUMENTATION PACKAGE

71

6

-

2

2

2

2

2

2-18032-2

SCR, SET, FLT POINT M3 X 10.0

70

6

-

1

-

-

1

1

2119740-1

TAG, IDENTIFICATION

67

6

-

2

2

2

2

2

2168078-1

SCREW, DRIVE, RH, RoHS, 2 x .188

66

6

-

1

1

1

1

1

1901681-5

HOLDDOWN, TERMINAL

65

6

-

1

-

1

1

1

2119793-1

LIMITER, ADJUSTMENT BOLT

63

6

-

3

-

3

3

3

992763-5

SCR, SET, SOC, CONE POINT, M3 x 4.0

62

6

-

1

1

1

1

1

2079383-4

SCR, BHSC, RoHS (M4 X 8)

60

6

-

-

-

-

-

1

5-18022-5

SCR, HEX HD CAP, M4 X 6.0

59

6

-

-

-

-

-

1

2063961-7

FEED FINGER

58

6

-

4

4

4

4

4

2168400-4

SHCS, LOW HEAD, RoHS, M4 X 8

57

6

-

2

2

2

2

2

1-2168083-0

SCR, SKT HD CAP, RoHS, M4 X 10

56

6

-

2

2

2

2

2

5018030-1

NUT, HEX, REG, RoHS, M3

54

6

-

2

2

2

2

2

986965-8

NUT, LOCK, HEX, TORQUE (M4)

53

6

-

1

1

1

1

1

1-5018030-0

NUT, HEX, REG, RoHS, M3.5

52

6

-

-

-

-

1

-

1-2119792-4

PAWL, EF, AIR

51

6

-

-

-

-

1

2

18023-9

SCR, SKT HD CAP M4 X 6.0

49

6

-

-

-

-

-

1

2119652-1

FEED CAM, PRE FEED

48

6

-

-

-

-

-

1

2119653-1

FEED CAM, POST FEED

47

6

-

1

1

1

1

1

2119655-5

APPLICATOR BASIC ASSEMBLY, EF

46

6

-

1

-

1

1

1

2119369-1

RAM, AMP STYLE, END FEED

44

6

-

1

1

1

1

1

2079383-7

SCR, BHSC, RoHS (M8 X 25)

41

6

-


1

-












1

1


LOC		DIST		REVISONS			
A	66	P	LYR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-




HOLDDOWN SET-UP




CAM POSITIONS



MECHANICAL POST FEED



MECHANICAL PRE FEED



AIR FEED

ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		OWN B. WEAVER 05MAY2017		TE Connectivity	
mm		0 PLC ±		CM T. ELBIN 05MAY2017		Harrisburg, PA 17105-3608	
		1 PLC ±		APVD T. ELBIN 05MAY2017		NAME	
		2 PLC ±		PRODUCT SPEC		Ocean End Feed	
		3 PLC ±		APPLICATION SPEC		Applicator	
		4 PLC ±		WEIGHT		SIZE	
MATERIAL		FINISH		Customer Accessible Production Drawing		CAGE CODE DRAWING NO	
				SCALE		A1 00779 C=2150800	
				SHEET		2 of 4	
				REV		A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2150800-2](#)