

8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT 20		BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.	
PART NUMBER	REVISION	DESCRIPTION	FEED TYPE
2151096-1	M	FINE CRIMP HEIGHT ADJUST	MECHANICAL
2151096-2	M	FINE CRIMP HEIGHT ADJUST	PNEUMATIC
5-2151096-1	M	SEAL STRIPPER CRIMPER TERMINATING UNIT	MECHANICAL
5-2151096-2	M	SEAL STRIPPER CRIMPER TERMINATING UNIT	PNEUMATIC
7-2151096-1	M	MECHANICAL AND CRIMP TOOLING KIT	MECHANICAL
7-2151096-2	M	PNEUMATIC AND CRIMP TOOLING KIT	PNEUMATIC
7-2151096-7	H	CRIMP TOOLING KIT	-

APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	1.57 mm [.062]	F
INSUL	3.18 mm [.125]	F
APPLICATOR INSTRUCTIONS 408-35042		


TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: VAL-U-LOK PIN CONTACT			
WIRE STRIP LENGTH 3.00-3.50 mm[.118-.138 IN]			INSULATION DIAMETER RANGE Ø 1.50-3.30 mm[.059-.130 IN]
TERMINAL APPLICATION SPECIFICATION	114-13172	-	-
	-	-	-
TERMINALS APPLIED  			
TE TERMINAL	TE TERMINAL	TE TERMINAL	TE TERMINAL
794955-1	794955-2	794955-3	794955-4
794956-1	794956-2	794956-3	794956-4
794956-5			

WIRE SIZE	CRIMP HEIGHT mm [INCH]	CRIMP HEIGHT REFERENCE SETTING
22 AWG + 20 AWG	1.22+/-0.05 [.048+/- .002]	4.1
17.45 AWG OR 0.936mm2	1.17+/-0.05 [.046+/- .002]	5.6
18 AWG OR 0.87mm2	1.09+/-0.05 [.043+/- .002]	5.8
2 X 22 AWG	1.09+/-0.05 [.043+/- .002]	5.8
20 AWG OR 0.50mm2	0.99+/-0.05 [.039+/- .002]	6.8
22 AWG OR 0.35mm2	0.80+/-0.05 [.031+/- .002]	7.7



- 1 RECOMMENDED SPARE PARTS
- 2 REFER TO SUPPLIED INSTRUCTION SHEET FOR CLEANING, LUBRICATION AND STORAGE OF APPLICATOR.
- 3 APPLY PART NUMBER 1-23419-5 LOCTITE TO THREADS OF ITEMS 180. APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.
- 4 CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.
- 5 INSTALL ITEM 3 AS SHOWN FOR TERMINALS 2238016 AND 2238017.
- 6 INSTALL ITEM 3 WITH RELIEF INWARDS AGAINST ITEM 1 FOR TERMINALS 794955 AND 794956.
- 7 TERMINAL LUBRICANT IS RECOMMENDED.
8. UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.

ATLANTIC VERSION TERMINATOR
INTERFACE ADAPTER



TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: VAL-U-LOK PIN CONTACT			
WIRE STRIP LENGTH 3.00-3.50 mm [.118-.138 IN]			INSULATION DIAMETER RANGE Ø 1.50-3.30 mm [.059-.130 IN]
TERMINAL APPLICATION SPECIFICATION 		114-13172	-
		-	-
TERMINALS APPLIED 			
TE TERMINAL	TE TERMINAL	TE TERMINAL	TE TERMINAL
2238016-1	2238017-1	2825210-1	2825211-1


WIRE SIZE	CRIMP HEIGHT mm [INCH]	CRIMP HEIGHT REFERENCE SETTING
22 AWG + 20 AWG	1.22+/-0.05 [.048+/- .002]	4.1
18 AWG OR 0.87mm2	1.09+/-0.05 [.043+/- .002]	5.8
2 X 22 AWG	1.09+/-0.05 [.043+/- .002]	5.8
20 AWG OR 0.50mm2	0.99+/-0.05 [.039+/- .002]	6.8
22 AWG OR 0.35mm2	0.80+/-0.05 [.031+/- .002]	7.7

*WARNING
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING, REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)


2		1						
LOC	DIST	REVISIONS						
A	66	P	LTR	DESCRIPTION		DATE	DWN	APVD
			K	ECR-18-009001		11JUN2018	JAH	JDG
			L	ECR-18-019939		20DEC2018	TB	TE
			L1	ECR-19-006483		23APR2019	FL	CT
			M	ECR-19-018162		20NOV2019	TB	TE

-	-	-	1	1	-	-	1803515-3	RAM ASSEMBLY, SF ATLANTIC	293
-	-	-	1	1	-	-	2-1803583-1	APPLICATOR BASIC ASSEMBLY, SF	292
-	1	-	1	-	1	-	2119641-1	FEED CAM, AIR FEED	248
-	1	1	1	1	1	1	2119082-9	CAM, SNAIL, INSULATION ADJUSTMENT	244
-	1	1	1	1	1	1	2079764-1	WASHER, WAVE SPRING, CREST-TO-CREST	243
-	1	1	1	1	1	1	2119083-1	RETAINER, INSULATION DIAL	242
-	1	1	1	1	1	1	7-18023-7	SCR, SKT HD CAP M3 X 4.0	241
-	-	1	-	1	-	1	2119580-1	MECHANICAL FEED ASSEMBLY	239
-	1	-	1	-	1	-	2844940-1	AIR FEED MODULE	238
-	-	-	1	1	-	-	4-1722335-3	STRIPPER, SIDE FEED	182
-	-	-	1	1	-	-	1-5018030-0	NUT, HEX, REG, RoHS, M3.5	181
-	-	-	1	1	-	-	1-1752354-9	STANDOFF,HOLD-DOWN	180
-	-	-	1	1	-	-	993111-1	PIN, SLOTTED SPRING 3.0 X 20.0	177
-	-	-	1	1	-	-	5-22280-0	SPRING, COMPRESSION	176
-	-	-	1	1	-	-	1752353-3	GUIDE PIN,HOLDDOWN	175
-	-	-	1	1	-	-	1901680-2	GUIDE PIN,HOLDDOWN	174
-	REF	REF	REF	REF	REF	REF	994970-2	COUNTER, MAGNETIC	164
-	1	1	1	1	1	1	2119955-1	ASSY, LUBRICATOR, SIDE FEED	113
-	1	1	1	1	1	1	2844908-1	SCREW, LOCKING	99
-	1	1	1	1	1	1	2844907-1	POST, LOCKING	98
-	1	1	1	1	1	1	1-455888-1	SPACER, CRIMPER	82
-	1	1	1	1	1	1	1803607-3	DOCUMENTATION PACKAGE	71
-	1	1	1	1	1	1	2119791-5	DEPRESSOR, WIRE	70
-	1	1	1	1	1	1	2119740-1	TAG,IDENTIFICATION	67
-	2	2	2	2	2	2	2168078-1	SCREW, DRIVE, RH, RoHS, 2 x .188	66
-	1	1	1	1	1	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	60
-	1	1	1	1	1	1	5-18022-5	SCR, HEX HD CAP, M4 X 6.0	59
-	1	1	1	1	1	1	1338685-1	PAWL, FEED	56
-	4	4	4	4	4	4	2168083-3	SCR, SKT HD CAP, RoHS, M4 X 12.0	54
-	2	2	2	2	2	2	1-2168083-0	SCR, SKT HD CAP, RoHS, M4 X 10	53
-	1	1	1	1	1	1	1803382-6	HOLD DOWN, SPRING LOADED	50
-	1	2	1	2	1	2	18023-9	SCR, SKT HD CAP M4 X 6.0	49
-	-	1	-	1	-	1	2119652-1	FEED CAM, PRE FEED	48
-	-	1	-	1	-	1	2119653-1	FEED CAM, POST FEED	47
-	1	1	-	-	1	1	1803583-9	APPLICATOR BASIC ASSEMBLY, SF	46
-	1	1	-	-	1	1	1803515-1	RAM ASSEMBLY, SF ATLANTIC	44
-	1	1	1	1	1	1	1803602-1	SCR, BHSC, RoHS (M8 X 25)	41
-	1	1	1	1	1	1	1752356-1	SUPPORT, TERMINAL	34
-	2	2	2	2	2	2	2079383-5	SCR, BHSC, RoHS (M4 X 20)	33
-	2	2	2	2	2	2	2-2844962-4	SPACER, CYLINDRICAL, STRIP GUIDE	30
-	1	1	1	1	1	1	2844992-1	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	1	1	1320928-2	STRIP GUIDE	24
-	1	1	-	-	1	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	21
-	2	2	1	1	2	2	1-18028-2	WASHER, FLAT, REG M4	20
-	1	1	-	-	1	1	2119533-1	STRIPPER, SIDE FEED	19
-	1	1	1	1	1	1	2119806-1	INSERT, SHEAR	13
-	1	1	1	1	1	1	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	1	1	1-356885-4	STOP, SHEAR	11
-	1	1	1	1	1	1	2119805-1	SHEAR HOLDER, FRONT	10
-	1	1	1	1	1	1	1803095-6	FLOATING SHEAR, FRONT -	9
1	2	2	1	1	1	1	8-1333202-5	ANVIL, COMBINATION	8
-	1	1	1	1	1	1	3-240641-8	SPACER	7
-	-	-	-	-	-	-	-	-	6
-	1	1	1	1	1	1	2119757-1	DEPRESSOR, SHEAR	5
-	1	1	1	1	1	1	1-238011-7	BLOCK, CRIMPER SPACER	4
1	2	2	1	1	1	1	9-2119582-0	CRIMPER, INSULATION F PREMIUM	3
-	-	-	-	-	-	-	-	-	2
1	2	2	1	1	1	1	4-456403-2	CRIMPER, WIRE PREMIUM	1

-77 -72 -71 -52 -51 -2 -1							PART NO		DESCRIPTION				ITEM NO	
THIS DRAWING IS A CONTROLLED DOCUMENT FOR TFC ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND WITHOUT LIABILITY. THE USER SHALL BE RESPONSIBLE FOR THE LATEST EDITION.							DWN	10NOV2011			TE Connectivity Harrisburg, PA 17105-3608			
							CHK	10NOV2011						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		L.ZHANG	10NOV2011	NAME								
				APVD	10NOV2011	Ocean Side Feed Applicator								
				S.XI										
mm				PRODUCT SPEC										
		0 PLC ±.1 1 PLC ±.1 2 PLC ±.1 3 PLC ±.1 4 PLC ±.1 ANGLES ±.1		APPLICATION SPEC		SIZE	CASE CODE	DRAWING NO	RESTRICTED TO					
MATERIAL		FINISH		WEIGHT		A1	00779	©=2151096						
Customer Accessible Production Drawing							SCALE	1:2	SHEET	1	OF	4	REV	M

SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION

PNEUMATIC



DETAIL A

30mm STROKE

40mm STROKE

MECHANICAL POST FEED

47

49

30mm STROKE

40mm STROKE

MECHANICAL PRE FEED

48

49



30mm STROKE

40mm STROKE


AIR FEED

248


49



TERMINAL SUPPORT LOCATION




RAM AND HOLDDOWN SET-UP



FEED TRACK POSITION
GUIDE BY INSULATION BARREL

Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

*THIS DRAWING IS A STANDARD DOCUMENT FOR TE CONNECTIVITY CORPORATION DRAWING IS TO CONFORM TO THE REQUIREMENTS OF THE INTERNATIONAL ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION				DWN: L. ZHANG 10NOV2011		 TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK: L. ZHANG 10NOV2011			
		0 PLC ±.		APP'D: S. XI 10NOV2011		NAME Ocean Side Feed Applicator	
		1 PLC ±.		PRODUCT SPEC			
		2 PLC ±.		APPLICATION SPEC			
		3 PLC ±.				SIZE CAGE CODE DRAWING NO	
		4 PLC ±.					
		ANGLES ±.					
MATERIAL -		FINISH -		WEIGHT -		A 00779 C=2151096	
Customer Accessible Production Drawing							
				SCALE 1:2		SHEET 2 of 4	
				REV M			

8	7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION
20		20
COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		
PART NUMBER	REVISION	DESCRIPTION
2-2151096-1	M	FINE CRIMP HEIGHT ADJUST
2-2151096-2	M	FINE CRIMP HEIGHT ADJUST
7-2151096-7	H	CRIMP TOOLING KIT
		FEED TYPE
		MECHANICAL
		PNEUMATIC
		-

PACIFIC VERSION TERMINATOR
INTERFACE ADAPTER




APPLICATOR DATA		
CRIMP	SIZE	TYPE
WIRE	1.57 mm [.062]	F
INSUL	3.18 mm [.125]	F
APPLICATOR INSTRUCTIONS		
408-35042		

TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: VAL-U-LOK PIN CONTACT			
WIRE STRIP LENGTH			INSULATION DIAMETER RANGE
3.00-3.50 mm [.118-.138 IN]		Ø	1.50 - 3.30 mm [.059-.130 IN]
TERMINAL APPLICATION SPECIFICATION	114-13172	-	-
TERMINALS APPLIED 			
TE TERMINAL	TE TERMINAL	TE TERMINAL	TE TERMINAL
794955-1	794955-2	794955-3	794955-4
794956-1	794956-2	794956-3	794956-4
794956-5			

WIRE SIZE		CRIMP HEIGHT mm [INCH]		CRIMP HEIGHT REFERENCE SETTING
22 AWG + 20 AWG		1.22+/-0.05 [.048+/- .002]		4.1
17.45AWG OR 0.936mm2		1.17+/-0.05 [.046+/- .002]		5.6
18 AWG OR 0.87mm2		1.09+/-0.05 [.043+/- .002]		5.8
2 X 22 AWG		1.09+/-0.05 [.043+/- .002]		5.8
20 AWG OR 0.50mm2		0.99+/-0.05 [.039+/- .002]		6.8
22 AWG OR 0.35mm2		0.80+/-0.05 [.031+/- .002]		7.7



- 1 RECOMMENDED SPARE PARTS
- 2 REFER TO SUPPLIED INSTRUCTION SHEET FOR CLEANING, LUBRICATION AND STORAGE OF APPLICATOR.
- 3 APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.
- 4 CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.
- 5 INSTALL ITEM 3 AS SHOWN FOR TERMINALS 2238016 AND 2238017.
- 6 INSTALL ITEM 3 WITH RELIEF INWARDS AGAINST ITEM 1 FOR TERMINALS 794955 AND 794956.
- 7 TERMINAL LUBRICANT IS RECOMMENDED.
8. UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.

TERMINAL DATA: TE TERMINAL		TE CRIMP SPECIFICATION	
TERMINAL NAME: VAL-U-LOK PIN CONTACT			
WIRE STRIP LENGTH			INSULATION DIAMETER RANGE
3.00-3.50 mm [.118-.138 IN]			Ø 1.50 - 3.30 mm [.059 -.130 IN]
TERMINAL APPLICATION SPECIFICATION		114-13172	-
		-	-
TERMINALS APPLIED			
			
TE TERMINAL	TE TERMINAL	TE TERMINAL	TE TERMINAL
2238016-1	2238017-1	2825210-1	2825211-1

WIRE SIZE		CRIMP HEIGHT mm [INCH]		CRIMP HEIGHT REFERENCE SETTING
22 AWG + 20 AWG		1.22+/-0.05 [.048+/- .002]		4.1
18 AWG OR 0.87mm2		1.09+/-0.05 [.043+/- .002]		5.8
2 X 22 AWG		1.09+/-0.05 [.043+/- .002]		5.8
20 AWG OR 0.50mm2		0.99+/-0.05 [.039+/- .002]		6.8
22 AWG OR 0.35mm2		0.80+/-0.05 [.031+/- .002]		7.7

*WARNING
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING, REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

LOC	DIST	REVISONS			
A	66	P	LTR	DESCRIPTION	DATE
		-		SEE SHEET 1	-

	-	1	1	2119082-9	CAM, SNAIL, INSULATION ADJUSTMENT	244
	-	1	1	2079764-1	WASHER, WAVE SPRING, CREST-TO-CREST	243
3	-	1	1	2119083-1	RETAINER, INSULATION DIAL	242
	-	1	1	7-18023-7	SCR, SKT HD CAP M3 X 4.0	241
	-	-	1	2119580-1	MECHANICAL FEED ASSEMBLY	239
	-	1	-	2844940-1	AIR FEED MODULE	238
	-	REF	REF	994970-2	COUNTER, MAGNETIC	164
	-	1	-	2119641-2	FEED CAM, AIR FEED	151
	-	1	1	2168083-8	SCR, SKT HD CAP, RoHS, M4 X 16	144
	-	4	4	2168083-9	SCR, SKT HD CAP, RoHS, M4 X 20	143
	-	-	1	2119653-2	FEED CAM, POST FEED	142
	-	1	1	1-1803583-0	APPLICATOR BASIC ASSEMBLY, SF	141
	-	1	1	1803516-1	RAM ASSEMBLY, SF PACIFIC	140
7	-	1	1	2119955-1	ASSY, LUBRICATOR, SIDE FEED	113
	-	1	1	2844908-1	SCREW, LOCKING	99
	-	1	1	2844907-1	POST, LOCKING	98
	-	1	1	1-455888-1	SPACER, CRIMPER	82
	-	1	1	1803607-3	DOCUMENTATION PACKAGE	71
	-	1	1	2119791-5	DEPRESSOR, WIRE	70
	-	1	1	2119740-1	TAG IDENTIFICATION	67
	-	2	2	2168078-1	SCREW, DRIVE, RH, RoHS, 2 x .188	66
	-	1	1	5-18022-5	SCR, HEX HD CAP, M4 X 6.0	59
	-	1	1	1338685-1	PAWL, FEED	56
	-	2	2	1-2168083-0	SCR, SKT HD CAP, RoHS, M4 X 10	53
	-	1	1	1803382-6	HOLD DOWN, SPRING LOADED	50
	-	1	2	18023-9	SCR, SKT HD CAP M4 X 6.0	49
	-	-	1	2119652-1	FEED CAM, PRE FEED	48
	-	1	1	1803602-1	SCR, BHSC, RoHS (M8 X 25)	41
	-	1	1	1752356-1	SUPPORT, TERMINAL	34
	-	2	2	2079383-5	SCR, BHSC, RoHS (M4 X 20)	33
	-	2	2	2-2844962-4	SPACER, CYLINDRICAL, STRIP GUIDE	30
	-	1	1	2844992-1	ASSEMBLY, STRIP GUIDE	29
	-	1	1	1320928-2	STRIP GUIDE	24
	-	1	1	2168083-2	SCR, SKT HD CAP, RoHS, M4 X 8.0	21
	-	2	2	1-18028-2	WASHER, FLAT, REG M4	20
	-	1	1	2119533-1	STRIPPER, SIDE FEED	19
1	-	1	1	2119806-1	INSERT, SHEAR	13
	-	1	1	3-22280-3	SPRING, COMPRESSION	12
	-	1	1	1-356885-4	STOP, SHEAR	11
1	-	1	1	2119805-1	SHEAR HOLDER, FRONT	10
1	-	1	1	1803095-6	FLOATING SHEAR, FRONT -	9
1	1	1	1	8-1333202-5	ANVIL, COMBINATION	8
	-	1	1	3-240641-8	SPACER	7
	-	-	-	-	-	6
	-	1	1	2119757-1	DEPRESSOR, SHEAR	5
	-	1	1	1-238011-7	BLOCK, CRIMPER SPACER	4
1	1	1	1	9-2119582-0	CRIMPER, INSULATION F PREMIUM	3
	-	-	-	-	-	2
1	1	1	1	4-456403-2	CRIMPER, WIRE PREMIUM	1
	-77	-22	-21	PART NO	DESCRIPTION	ITEM NO

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE USER SHALL BE RESPONSIBLE FOR OBTAINING THE LATEST EDITION.		DWN L.ZHANG 10NOV2011	STE TE Connectivity Harrisburg, PA 17105-3608	
CHK L.ZHANG 10NOV2011		NAME		
APVD S.XI 10NOV2011		PRODUCT SPEC		
DIMENSIONS: mm		APPLICATION SPEC		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		WEIGHT		
MATERIAL		SIZE CASE CODE DRAWING NO		RESTRICTED TO
		A1 00779 C=2151096		
Customer Accessible Production Drawing		SCALE 1:2		SHEET 3 OF 4 REV M

SHEETS 1 & 2 ARE NOT REQUIRED FOR PACIFIC VERSION

DETAIL A

30mm STROKE

142

49

MECHANICAL POST FEED

30mm STROKE

48

49

MECHANICAL PRE FEED


30mm STROKE

151

49

AIR FEED

Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

THIS DRAWING IS A COMPUTER GENERATED FILE. ALL DIMENSIONS AND TOLERANCES ARE BASED ON THE LATEST REVISION. ANY CHANGES TO THE DESIGN SHALL BE REFLECTED IN THE LATEST REVISION.									
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		DWN: 10NOV2011 CHK: L. ZHANG 10NOV2011 APP: S. YI 10NOV2011		 TE Connectivity Morrisburg, PA 17105-3608			
mm		0 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±°		NAME: Ocean Side Feed Applicator		SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO:			
		FINISH:		APPLICATION SPEC:		WEIGHT:			
MATERIAL:		-		A 00779 C=2151096		SCALE: 1:2 SHEET 4 OF 4 REV M			
Customer Accessible Production Drawing									

SHEETS 1 & 2 ARE NOT REQUIRED FOR PACIFIC VERSION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2151096-2](#)