

REV. 0

DCO 15961

TOLERANCES = $\pm .010$

COIL: @ 25°C
 RESISTANCE 27 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC

MUST RELEASE 1.65 VDC MAX, 0.29 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C


NOTES: OPERATE & RELEASE 4 MS MAX.

CONTACT BOUNCE 2.0 MS MAX.

CONTACT STABILIZATION 2.0 MS MAX.

ALL OTHER REQUIREMENTS TO MIL-R-39016 LEVEL M

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 12/6/99 CK. SAH 12/6/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/6-147M REV. ----

"HFW" RELAY

HFW1230L03M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HFW1230L03M](#)