

REV. 0

DCO 143761

COIL: @ 25°C

RESISTANCE 125 OHMS ±10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.8 VDC

MUST RELEASE 1.7 VDC MAX., 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.

RELEASE TIME 7.5 MS MAX.

CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 25JUN03

CK [Signature] 6/6/03

**CII Technologies**  
advanced control electronics solutions

CUST. DPL

CUST. NO. M39016/25-041M

REV.

"J1MSD" RELAY

J1MSCD-5XMS

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[J1MSCD-5XMS](#) [3-1617565-7](#)