

REV. 0

DCO 142073

COIL: @ 25°C  
 RESISTANCE \_\_\_\_\_ 4000 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE \_\_\_\_\_ 26.5 VDC  
 MUST OPERATE \_\_\_\_\_ 15.4 VDC  
 \_\_\_\_\_  
 MUST RELEASE \_\_\_\_\_ 8.0 VDC MAX. 1.37 VDC MIN.

ENVIRONMENT:


VIBRATION \_\_\_\_\_ 10 \_\_\_\_\_ CPS TO \_\_\_\_\_ 3000 CPS @ \_\_\_\_\_ 30 g's  
 SHOCK \_\_\_\_\_ 75 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION  
 TEMPERATURE \_\_\_\_\_ -65 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C

NOTES: \_\_\_\_\_ OPERATE TIME 4.0 MS MAX.

\_\_\_\_\_ RELEASE TIME 7.5 MS MAX.

\_\_\_\_\_ CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 6/6/00

ER. [Signature] 6/6/00

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. \_\_\_\_\_ OPL  
 CUST. NO. M39016/26-036P REV. \_\_\_\_\_

J1MSDD RELAY

J1MSCDD-26XP

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[J1MSCDD-26XP](#)