

REV. 0

DCO 142932

COIL: @ 25°C

RESISTANCE

3200 OHMS  $\pm$ 10%

NOMINAL VOLTAGE

26.5 VDC

MUST OPERATE

15.2 VDC

MUST RELEASE

10.8 VDC MAX, 1.7 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 7.5 MS MAX

CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. PBB 5/14/01

CK *[Signature]* 5/14/01

**CII Technologies**  
advanced control electronic solutions

CUST. OPL

CUST. NO. M39016/43-038P REV.

"JMGSCDD" RELAY

JMGSCDD-26P

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMGSCDD-26P](#) [2-1617150-4](#)