


NOTE:


- ① MOLD TE LOGO .062±.015 [1.57±0.38] HIGH CHARACTERS
LOCATED APPROX AS SHOWN
- ② MOLD CAVITY IDENT (MOLDED IN) .046±015 [1.15±0.38] HIGH CHARACTERS
LOCATED APPROX AS SHOWN
- ③ RECESSED AREA AROUND MOLD GATE IS OPTIONAL. THIS FEATURE IS
ALLOWABLE ON EITHER SIDE OF HOUSING OR MAY NOT BE PRESENT AT ALL.
- ④ COORDINATE DIMENSION APPLIES FROM CENTER
OF FIRST ACTUAL FEATURE
- ⑤ RECESSED AREA AROUND GATE PERMISSIBLE. THIS FEATURE IS
ALONG CENTERLINE OF MATING FACE.

6. WHEN MATING WITH AMP-LATCH UNIVERSAL HEADERS, P/N 1825851-1 MUST BE
USED. PURCHASE SEPARATELY WITH HEADER- 2 REQUIRED.

- ⑦ VOID CORING IS OPTIONAL, AT MOLDER'S DISCRETION.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MOYER 5-17-89		 TE Connectivity	
		CHK K. HELM 6-13-89			
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HOUSING, CRIMP SNAP-IN, SHORT ENTRY, MOD IV -	
		APVD			
		PRODUCT SPEC 108-25020			
0 PLC ± 1 PLC ± 2 PLC ± 4 PLC ±0.005[0.13] ANGLES ±		APPLICATION SPEC 114-25003, 114-25016		SIZE A2	
MATERIAL FLAME RETARDANT THERMOPLASTIC COLOR: BLACK PER ASTM D4066		FINISH -		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C=102387	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 4:1 SHEET OF REV U	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-102387-0](#)