


COIL: @ 25°C
 RESISTANCE 1600 OHMS \pm 10%
 NOMINAL VOLTAGE 18.0 VDC
 MUST OPERATE 10.0 VDC
 TURN-ON BASE CURRENT .09 mADC
 MUST RELEASE 6.0 VDC MAX, 0.91 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 4.0 MS MAX
 TURN-OFF TIME 7.5 MS MAX
 CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
 1A 28 VDC RESISTIVE 100,000
 OPERATIONS

DR. R.B. 6/24/98 *ER* 6/24/98

**COMMUNICATIONS
 INSTRUMENTS, INC.**

JMSCT-18XPS

CUST. QPL
 CUST. NO. M28776/3-045P

TYPE JMST RELAY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMSCT-18XPS](#)