

REV. 0
DCO 142821

COIL: @ 25°C
RESISTANCE _____ 100 OHMS $\pm 10\%$
NOMINAL VOLTAGE _____ 5.0 VDC
MUST OPERATE _____ 2.6 VDC

MUST RELEASE _____ 1.4 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 CPS TO _____ 3000 CPS @ _____ 30 g's

SHOCK _____ 75 g's _____ 6 MS. DURATION


TEMPERATURE _____ -65 °C TO _____ +125 °C

NOTES: _____ OPERATE TIME 4.0 MS MAX

_____ RELEASE TIME 7.5 MS MAX

_____ CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: _____ LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 3/15/01

3/15/01

ICH Technologies
advanced control electronic solutions

CUST. _____ QPL
CUST. NO. M39016/16-017P REV. _____

"JMSD" RELAY

JMSWD-5XP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMSWD-5XP](#)