

REV. 0
DCO 143283

COIL: @ 25°C
RESISTANCE 220 OHMS ±10%
NOMINAL VOLTAGE 9.0 VDC
MUST OPERATE 5.3 VDC
MUST RELEASE 0.54 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.

RELEASE TIME 1.5 MS MAX.

CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 10/25/01 CK 10/25/01

CII Technologies
advanced control electronic solutions

CUST. CII
CUST. NO. STANDARD REV.

"MA" RELAY

MAC - 9W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MAC-9W](#)