

COIL: @ 25°C

RESISTANCE 850 OHMS  $\pm$  10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 64 VDC

#### ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX

RELEASE TIME 2 MS MAX

CONTACT BOUNCE 1.5 MS MAX

#### CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 4/5/95 [Signature]

**COMMUNICATIONS  
INSTRUMENTS, INC.**

CUST. C. I. I.  
CUST. NO. STD.

TYPE 'MS' RELAY

**MSW-12**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MSW-12](#)