

REV. 0


DCO 141346

COIL: @ 25°C  
 RESISTANCE \_\_\_\_\_ 50 OHMS ±10%  
 NOMINAL VOLTAGE \_\_\_\_\_ 5.0 VDC  
 MUST OPERATE \_\_\_\_\_ 2.7 VDC  
 \_\_\_\_\_ 1.4 VDC MAX, 0.22 VDC MIN.  
 MUST RELEASE \_\_\_\_\_

ENVIRONMENT: 10 3000 30  
 VIBRATION \_\_\_\_\_ 75 CPS TO \_\_\_\_\_ 6 CPS @ \_\_\_\_\_ g's  
 SHOCK \_\_\_\_\_ g's \_\_\_\_\_ MS. DURATION  
 \_\_\_\_\_ -65 °C TO \_\_\_\_\_ +125 °C  
 TEMPERATURE \_\_\_\_\_ °C TO \_\_\_\_\_ °C

NOTES: OPERATE TIME 2 MS MAX  
 RELEASE TIME 4 MS MAX  
 CONTACT BOUNCE 1.5 MS MAX

## CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 9/14/99 CK. 9/14/99

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. C.I.I.  
 CUST. NO. STANDARD REV.

PRMAD RELAY

PRMAPD-5X

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PRMAPD-5X](#)