

REV. 4 8/25/98

COIL: @ 25°C

RESISTANCE 100 OHMS \pm 10%

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.6 VDC

MUST RELEASE 0.23 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 2.0 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. R.B. 6/3/97 *CK* *8/25/98*

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. TELEDYNE
CUST. NO. ER134M4-5A

TYPE PRMGS RELAY

PRMGSC-5XW

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PRMGSC-5XW](#)