

COIL: @ 25°C
 RESISTANCE 100 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.6 VDC
 MUST RELEASE 0.23 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX
 RELEASE TIME 7.5 MS MAX
 CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
 28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. R.B. 8/6/98 CK. XERRY 8/6/98

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. TELEDYNE
 CUST. NO. ER134DM4-5A

TYPE PRMGSD RELAY

PRMGSCD-5XW

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PRMGSCD-5XW](#)