


- Locking system for standardized IEC C14/C20 inlet filter
- No accidental disconnection
- Rated current up to 10 A (C13 plug), up to 15 A (C13P plug), and up to 20 A (C19 plug)
- Fits any Schaffner IEC C14/C20 inlet filter
- Retrofit for any IEC C14/C20 inlet
- Various power line plugs for international usage



The locking system has a tensile force of typical 200N. It is recommended to use it with flange mount filters. For details refer to our Application Note "Using IEC Lock Power Cords with IEC Inlets and Filters"

Schaffner power cords with IEC lock guard against accidental disconnection of all electrical appliances with an IEC inlet. No exchange or modification of the IEC inlet or IEC inlet filter system is needed. Easy retrofit for all electronic equipments and devices.

Maximum continuous operating voltage	250 VAC, 50/60 Hz
Nominal operating voltage	230 VAC
Rated currents	10 A for C13 plug, 15 A for C13P plug
Operating frequency	DC to 60 Hz
High potential test voltage	P-> PE 2000 VAC (1 min 50 Hz) P-> N 2000 VAC (1 min 50 Hz)
Temperature range (operation and storage)	-25°C to +70°C
Protection category	IP 20 according IEC 60529
Flammability corresponding to	Plugs: UL 94 V-2 or better Cable: IEC 60332-1 Cat. F2
Connector (load side)	IEC C13 according to IEC/EN 60320-2-2 with IEC Lock UL 498, CSA C22.2 no. 42 (for cold conditions) pin temp. 70°C, up to 15 A, Protection Class I
Connector (line side) and cables	Please refer to table on page 2 and 3

- Power cord with locking system for IEC inlets
- Protection class I (IL 13, IL 13 P)
- Suitable for use with any C14 IEC inlet (IL 13, IL 13 P) and C20 IEC inlet (IL 19)
- Fits the complete Schaffner IEC inlet filter program with C14 IEC inlet and C20 IEC inlet (IL 19)
- Max. pin temperature 70°C

- Data centers
- Industrial equipment
- Medical devices
- In-vitro diagnostic devices
- Broadcasting stations
- Mobile applications

Maximum continuous operating voltage	250 VAC, 50/60 Hz
Rated currents	10 A for C13 plug, 15 A for C13P plug
High potential test voltage	P→ PE 2000 VAC (1 min 50 Hz) P → N 2000 VAC (1 min 50 Hz)
Protection category	IP 20 according IEC 60529
Temperature range (operation and storage)	-25°C to +70°C
Connector (load side)	IEC C13 according to IEC/EN 60320-2-2 with IEC Lock UL 498, CSA C22.2 no. 42 (for cold conditions) pin temp. 70°C, up to 15 A, Protection Class I
Connector (line side) and cables	Please refer to table on page 2 and 3
Flammability corresponding to	Plugs: UL 94 V-2 or better; Cable: IEC 60332-1 Cat. F2

Maximum continuous operating voltage	250 VAC, 50/60 Hz
Rated currents	16 A (IEC), 20 A (UL)
Operating frequency	50 to 400 Hz
High potential test voltage	P-> PE 2000 VAC (1 min 50 Hz) P -> N 2000 VAC (1 min 50 Hz)
Protection category	IP 20 according IEC 60529
Temperature range (operation and storage)	-25°C to +70°C
Connector (load side)	IEC C19 according to IEC/EN 60320-2-2 with IEC lock, UL 498, CSA C22.2 no. 42 (for cold conditions) pin temp. 70°C, up to 20 A, Protection Class I
Connector (line side) and cables	please refer to table on page 4
Flammability corresponding to	Plugs: UL 94 V-2 or better; Cable: IEC 60332-1 Cat. F2

Cable Selection Table IL13

IL13-C14-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, EU version
IL13-C14-SVT-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, US version
IL13-CH1-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, CH version
IL13-EU1-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, EU version
IL13-JP1-HVCTF-3125-X*	IEC cable assembly with locking system for IEC C14 inlet, JP version
IL13-SE-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, stripped ends
IL13-UK1-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, UK version
IL13-US1-SVT-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, US version
IL13-US2-SJT-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, US version, hospital grade

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):

- X* options = 200, 300, 400, 500 or 1000 cm; 183, 275 or 366 cm (6, 9 or 12 feet)

Available Combinations IL13

To compile a complete part number exchange the letters (IL13-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL13		Line side plug		Cable type		Cable core		Rating	Cable length*		Cable color		Cert.
IL13		yyy		zzz		aaaa			bbb		c		
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight Australian plug 3 pins SEV1011, straight CEE 7/II, right angled CEE 7/VII, straight Italian Plug Israel Plug Korean Plug South African Plug Stripped Ends BS1363, right angled fused 5A BS1363, right angled fused 10A	C14	H05VV-F	H05	3x1.00mm ²	3100	250VAC 10A	6 feet	183	Black Blue Orange Red White	- B O R W	CB KC KEMA SAA
			AU1						200 cm	200			
			CH1						9 feet	275			
			EU1						300 cm	300			
			EU2						12 feet	366			
			IT1						400 cm	400			
			IL1						500 cm	500			
			KC1						1000 cm	1000			
			SA1										
			SE										
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight Japanese Plug JIS C8303 insulated sleeves Stripped Ends	C14	HVCTF	HVCTF	3x1.25mm ² 3x2.00mm ²	3125 3200	125VAC	100 cm	100	Black Blue Orange Red White	- B O R W	PSE
			JP1					12A	200 cm	200			
			SE					15A	300 cm	300			
									400 cm	400			
									500 cm	500			
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight Stripped Ends NEMA5-15, straight NEMA5-15, straight, hospital grade	C14	SJT SVT	SJT SVT	AWG 18 AWG 16 AWG 14	3100 3130 3160	125VAC	6 feet	183	Black Blue Orange Red White	- B O R W	UL cUL
			SE					10A	200 cm	200			
								13A	9 feet	275			
								15A	300 cm	300			
									12 feet	366			
									400 cm	400			
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight Chinese plug Stripped Ends	C14	RVV	RVV	3x1.00mm ²	3100	250VAC			Black Blue Orange Red White	- B O R W	CCC
			CN1					10A	200 cm	200			
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight Indian plug 3 Pin Stripped Ends	C14	BIS 694 1000V	BIS694	3x1.00mm ²	3100	250VAC			Black Blue Orange Red White	- B O R W	CB
			IN1					10A	200 cm	200			

*feet values are calculated to the matching length in cm

Cable Selection Table IL13P

IL13P-C14-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, EU version
IL13P-CH1-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, CH version
IL13P-EU1-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, EU version
IL13P-JP1-HVCTF-3125-X*	IEC cable assembly with locking system + for IEC C14 inlet, JP version
IL13P-SE-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, stripped ends
IL13P-UK1-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, UK version
IL13P-US1-SJT-3160-X*	IEC cable assembly with locking system + for IEC C14 inlet, US version
IL13P-S-C14-UC-3100-X*	IEC SLIMLINE cable assembly with locking system + for IEC C14 inlet

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):

- X* options = 200, 300, 400, 500 or 1000 cm; 183, 275 or 366 cm (6, 9 or 12 feet)

Available Combinations IL13P

To compile a complete part number exchange the letters (IL13P-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL13P		Line side plug		Cable type		Cable core		Rating	Cable length*		Cable color		Cert.
IL13P			yyy		zzz		aaaa			bbb		c	
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Australian plug 3 pins SEV1011, straight CEE 7/VII, right angled CEE 7/VII, straight Italian Plug Israel Plug Korean Plug South African Plug Stripped Ends BS1363, right angled fused 5A BS1363, right angled fused 10A	C14	H05VV-F	H05	3x1.00mm²	3100	250VAC 10A	6 feet	183	Black Blue Orange Red White	- B O R W	CB KC KEMA SAA
			AU1						200 cm	200			
			CH1						9 feet	275			
			EU1						300 cm	300			
			EU2						12 feet	366			
			IT1						400 cm	400			
			IL1						500 cm	500			
			KC1						1000 cm	1000			
			SA1										
			SE										
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Japanese Plug JIS C8303 insulated sleeves Stripped Ends	C14	HVCTF	HVCTF	3x1.25mm² 3x2.00mm²	3125 3200	125VAC 12A 15A	100 cm	100	Black Blue Orange Red White	- B O R W	PSE
			JP1						200 cm	200			
			SE						300 cm	300			
									400 cm	400			
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Stripped Ends NEMA5-15, straight NEMA5-15, straight, hospital grade	C14	SJT SVT	SJT SVT	AWG 18 AWG 16 AWG 14	3100 3130 3160	125VAC 10A 13A 15A	6 feet	183	Black Blue Orange Red White	- B O R W	UL cUL
			SE						200 cm	200			
			US1						9 feet	275			
			US2						300 cm	300			
									12 feet	366			
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Chinese plug Stripped Ends	C14	RVV	RVV	3x1.00mm²	3100	250VAC 10A	200 cm	200	Black Blue Orange Red White	- B O R W	CCC
			CN1										
			SE										
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Indian plug 3 Pin Stripped Ends	C14	BIS 694 1000V	BIS694	3x1.00mm²	3100	250VAC 10A	200 cm	200	Black Blue Orange Red White	- B O R W	CB
			IN1										
			SE										
IL13P-S	IEC C13 + DUAL Locking Female plug, straight, lock	IEC C14 dual locking, male, straight	C14	H05VV-F	UC	3x1.00mm²	3100	250VAC 10A	50 cm	50	Black Blue Red White	- B R W	ENEC cUL SAA
									100 cm	100			
									150 cm	150			
									200 cm	200			
									250 cm	250			
									300 cm	300			

*feet values are calculated to the matching length in cm

New DUAL Locking Version IL13P-S



Locking functionality on both ends of the cord

Cable Selection Table IL19

IL19-C20-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, EU version
IL19-C20-SJT-3160-X*	IEC cable assembly with locking system for IEC C20 inlet, US version
IL19-EU1-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, EU version
IL19-SE-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, stripped ends
IL19-UK1-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, UK version
IL19-US1-SJT-3160-X*	IEC cable assembly with locking system for IEC C20 inlet, US version

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):

- X* options = 200, 300, 400, 500 or 1000 cm; 183, 275 or 366 cm (6, 9 or 12 feet)

Available Combinations IL19

To compile a complete part number exchange the letters (IL19-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL19		Line side plug		Cable type		Cable core		Rating*	Cable length**		Cable color		Cert.
IL19		yyy		zzz		aaaa			bbb		c		
IL19	IEC C19 Female plug, straight, lock	IEC C20, male, straight	C20	H05VV-F	H05	3x1.50mm ²	3150	16A	6 feet	183	Black Blue Orange Red White	- B O R W	CB KEMA SAA
		Australian plug 3 pins	AU1					15A	200 cm	200			
		SEV1011, straight	CH1					16A	9 feet	275			
		CEE 7/VII, right angled or straight	EU1					16A	300 cm	300			
		Italian Plug	IT1					16A	12 feet	366			
		South Africa plug	SA1					16A	400 cm	400			
		Stripped Ends	SE					16A	500 cm	500			
		BS1363, right angled fused 13A	UK1					13A	1000 cm	1000			
IL19	IEC C19 Female plug, straight, lock	IEC C20, male, straight	C20	HVCTF	HVCTF	3x2.00mm ²	3200	15A	100 cm	100	Black Blue Orange Red White	- B O R W	PSE
		Japanese Plug JIS C8303 insulated sleeves	JP1						200 cm	200			
		Stripped Ends	SE						300 cm	300			
									400 cm	400			
									500 cm	500			
IL19	IEC C19 Female plug, straight, lock	IEC C20, male, straight	C20	SJT SVT	SJT SVT	AWG14 AWG12	3160 3205	125V 15A 20A	6 feet	183	Black Blue Orange Red White	- B O R W	UL cUL
		Stripped Ends	SE						200 cm	200			
									9 feet	275			
		NEMA5-15, straight	US1						300 cm	300			
									12 feet	366			
		Nema 5-20P	US4						400 cm	400			
IL19	IEC C19 Female plug, straight, lock	Chinese plug	CN1	RVF	RVF	3x1.50mm ²	3150	16A	200 cm	200	black	-	CCC

* if not seperately mentioned 250VAC is rated voltage

** feet values are calculated to the matching length in cm

Headquarters, Global
Innovation and
Development

Switzerland
Schaffner Group
Industrie Nord
Nordstrasse 5
4542
Luterbach
+41 32 681 66 26
info@schaffner.com

To find your local partner within
Schaffner's global network [schaffner.com](https://www.schaffner.com)

© 2025 Schaffner Group

The content of this document has been carefully checked and understood. However, neither Schaffner nor its subsidiaries assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifications are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer. In all cases, products must never be operated outside their published specifications. Schaffner does not guarantee the availability of all published products. This disclaimer shall be governed by substantive Swiss law and resulting disputes shall be settled by the courts at the place of business of Schaffner Holding AG. Latest publications and a complete disclaimer can be downloaded from the Schaffner website. All trademarks recognized.

Sales and Application
Centers

China
Schaffner EMC Ltd. Shanghai
T20-3 C No 565 Chuangye Road Pudong district
201201
Shanghai
+86 2138139500
cschina@schaffner.com

Sweden
Schaffner EMC AB
Östermalmstrorg 1
114 42
Stockholm
+46 8 5050 2425
swedensales@schaffner.com

Switzerland
Schaffner EMV AG
Industrie Nord
Nordstrasse 5
4542
Luterbach
+41 32 681 66 26
switzerlandsales@schaffner.com

India
Schaffner India Pvt. Ltd
Regus World Trade Centre
WTC 22nd Floor Unit No 2238 Brigade
Gateway Campus 26/1 Dr. Rajkumar Road
Malleshwaram (W)
560055
Bangalore
+91 8067935355
indiasales@schaffner.com

Italy
Schaffner EMC S.r.l.
Via Ticino, 30
20900
Monza (MB)
+39 335 120 44 32
italysales@schaffner.com

Japan
Schaffner EMC K.K.
ISM Sangenjaya 7F
1-32-12 Kamiuma Setagaya-ku
154-0011
Tokyo
+81 3 5712 3650
japansales@schaffner.com

Singapore
Schaffner EMC Pte Ltd.
Blk 3015A Ubi Road 1 #05-09 Kampong Ubi
Industrial Estate
408705
Singapore
+65 63773283
singaporesales@schaffner.com

Finland
Schaffner Oy
Lohjanharjuntie 1109
08500
Lohja
+ 358 50 468 72 84
finlandsales@schaffner.com

France
Schaffner EMC S.A.S.
16-20 Rue Louis Rameau
95875
Bezons
+33 1 34 34 30 60
francesales@schaffner.com

Germany
Schaffner Deutschland GmbH
Ohiostr. 8
76149
Karlsruhe
+49 721 56910
germanysales@schaffner.com

Thailand
Schaffner EMC Co. Ltd.
Sathorn Square Tower
Room 3780 37FL 98 North-Sathorn Rd Silom
Bangrak
10500
Bangkok
+66 621056397
thailandsales@schaffner.com

United Kingdom
Schaffner Ltd.
Suite 1 Oakmede Place
Terrace Road
RG42 4JF
Binfield
+44 118 9770070
schaffner.uksales@te.com

United States
Schaffner EMC Inc.
52 Mayfield Avenue
Edison, New Jersey
+1 732 225 9533
usasales@schaffner.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[IL13-C14-SVT-3100-183](#) [IL13-EU1-H05-3100-200](#) [IL13-US1-SVT-3100-183](#) [IL13-UK1-H05-3100-200](#) [IL13-US2-SJT-3100-183](#) [IL13-US2-SJT-3100-275](#) [IL13-US2-SJT-3100-366](#) [IL13-EU1-H05-3100-300](#) [IL19-C20-H05-3150-200](#) [IL19-US1-SJT-3160-183](#) [IL13P-US1-SJT-3160-275](#) [IL19-UK1-H05-3150-200](#) [IL19-EU1-H05-3150-200](#) [IL13-EU1-H05-3100-400](#) [IL13-SE-H05-3100-500](#) [IL13P-US1-SJT-3160-366](#) [IL19-SE-H05-3150-200](#) [IL19-C20-SJT-3160-183](#) [IL13-US1-SVT-3100-366](#) [IL13P-US1-SJT-3160-183](#) [IL13-US1-SVT-3100-275](#) [IL13-C14-H05-3100-200](#) [IL13P-CH1-H05-3100-200](#) [IL13-BR1-H05-3100-100](#) [IL13-BR1-H05-3100-200](#) [IL13-SE-H05-3100-200](#) [IL13P-US1-SVT-3100-183](#) [IL13-C14-SJT-3100-300](#) [IL13-JP1-HVCTF-3125-200](#) [IL13-CH1-H05-3100-200](#) [IL13-JP1-IS-HVCTF-3125-200](#) [IL13P-EU1-H05-3100-300](#) [IL13P-R-US1-SVT-3100-275](#) [IL13P-U-CH1-H05-3100-300](#) [IL13P-U-EU1-H05-3100-300](#) [IL13P-U-EU2-H05-3100-300](#) [IL13P-U-US1-SJT-3160-300](#) [IL13P-U-US2-SJT-3160-300](#) [IL13P-D-UK1-H05-3100-300](#) [IL13P-D-US1-SJT-3160-300](#) [IL13P-D-CH1-H05-3100-300](#) [IL13P-D-SA1-H05-3100-300](#) [IL13P-D-EU1-H05-3100-300](#) [IL13P-D-US2-SJT-3160-300](#) [IL13P-R-C14-H05-3100-200](#) [IL13P-D-AU1-H05-3100-300](#) [IL13-SE-H05-3100-300](#)