

REV. 3  
DCO 63333


COIL: @ 25°C  
RESISTANCE \_\_\_\_\_ 390 OHMS ±10%  
NOMINAL VOLTAGE \_\_\_\_\_ 26.5 VDC  
MUST OPERATE \_\_\_\_\_ 14.0 VDC @ 25°C  
\_\_\_\_\_  
MUST RELEASE \_\_\_\_\_ 1.4 VDC @ 25°C

ENVIRONMENT:

VIBRATION \_\_\_\_\_ 10 \_\_\_\_\_ CPS TO \_\_\_\_\_ 2000 \_\_\_\_\_ CPS @ \_\_\_\_\_ 15 \_\_\_\_\_ g's  
SHOCK \_\_\_\_\_ 100 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION  
TEMPERATURE \_\_\_\_\_ -65 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C

NOTES: \_\_\_\_\_ OPERATE & RELEASE 7 MS MAX.  
\_\_\_\_\_  
(INCLUDING BOUNCE)

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: \_\_\_\_\_ LOW LEVEL TO  
\_\_\_\_\_ 2 AMP 28 VDC RESISTIVE

DR. R.B. 2/25/93

CK.TLG 10-24-00

**CI Technologies**  
advanced control electronic solutions

CUST. \_\_\_\_\_ QPL  
CUST. NO. \_\_\_\_\_ M39016/40-001 REV. \_\_\_\_\_

'SR' RELAY

SR-7601

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SR-7601](#)