

REV. 1

DCO 63333

COIL: @ 25°C  
 RESISTANCE \_\_\_\_\_ 25 OHMS ±10%  
 NOMINAL VOLTAGE \_\_\_\_\_ 6.0 VDC  
 MUST OPERATE \_\_\_\_\_ 3.2 VDC

MUST RELEASE \_\_\_\_\_ 2.1 VDC MAX, 0.46 VDC MIN.

#### ENVIRONMENT:

VIBRATION \_\_\_\_\_ 10 \_\_\_\_\_ CPS TO \_\_\_\_\_ 2000 \_\_\_\_\_ CPS @ \_\_\_\_\_ 15 \_\_\_\_\_ g's


SHOCK \_\_\_\_\_ 100 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION

TEMPERATURE \_\_\_\_\_ -65 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C

NOTES: \_\_\_\_\_ OPERATE & RELEASE 7 MS MAX.

(INCLUDING BOUNCE)

#### CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: \_\_\_\_\_ LOW LEVEL TO  
 \_\_\_\_\_ 2 AMP 28 VDC RESISTIVE  
 \_\_\_\_\_ 100,000 OPERATIONS

DR. R.B. 4/20/98

CK. TLG 10-24-00

**CII Technologies**  
 advanced control electronic solutions

CUST. \_\_\_\_\_ QPL

CUST. NO. \_\_\_\_\_ M39016/40-006 REV. \_\_\_\_\_

"SR" RELAY

SR-7606

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SR-7606](#)