

#### COIL:

RESISTANCE 390 OHMS ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 15.5 VDC @ 25°C

MUST RELEASE 1.8 VDC @ 25°C

#### ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: TERMINALS ARE GOLD-PLATED I.A.W.  
MIL-G-45204, TYPE II, CLASS I.

OPERATE & RELEASE TIME 5 MS MAX.

CONTACT BOUNCE 5 MS MAX.

#### CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
2 AMP / 28 VDC

DR. R.B. 11/4/91

CK. JAW/ 11-4-91

**COMMUNICATIONS**  
**INSTRUMENTS, INC.**

CUST. CTI SIO

CUST. NO. \_\_\_\_\_

TYPE 'SS' RELAY

**SSBW-6C-24G**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SSBW-6C-24G](#)