




Application Tooling > Magnet Wire Equipment



Magnet Wire Equipment Application: **Power Splice**

Crimp Height Adjustment Method: **Manual Crimp Height Adjustment**

Equipment Options: **None**

Features

Other

Automation Level	Manual Workstation
Magnet Wire Equipment Application	Power Splice
Crimp Height Adjustment Method	Manual Crimp Height Adjustment
Equipment Options	None

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2368878-1
POWER SPLICE APPLICATOR




TE Part # 1601953-1
111-000-001=SPLICE TERMINAL


Customers Also Bought




TE Part #2150368-2
OCEAN_2.0_Applicator-E-140F180F-SEA




TE Part #2150414-2
OCEAN_2.0_Applicator-E-110F155F-SEA




TE Part #2150348-2
OCEAN_2.0_Applicator-E-155F-REA




TE Part #1217973-2
TERM,SPLICE,MAG-MATE




TE Part #2217419-3
SPLICE TOOLING ASSEMBLY



TE Part #768690-4
ANVIL, WIRE



TE Part #768700-1
CRIMPER, WIRE



TE Part #2161677-2
CABLE, CAN BUS TO MOTOR



TE Part #679857-3
CRIMPER, WIRE "F"



TE Part #2217413-2
ANVIL

Documents

Datasheets & Catalog Pages

For Magnet Wire Processing 1-1773899-1

English

2338149-1 Best Practice for IDC Magnet Wire Termination

English

Instruction Sheets

Power Splice 20 (PS-20) Terminator, PN 2378104-[]

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2378104-2](#)