



10K3A1I SERIES II

Thermistor

SPECIFICATIONS

- Thermally conductive epoxy coating
- Ø 2.4 mm Maximum Diameter
- 30 AWG Solid Silver Plated Copper Leads with White PTFE Insulation
- Choice of 4 temperature tolerance classifications
- RoHS Compliant

The BetaCURVE Chip is Soldered to 30 AWG Solid Silver Plated Copper Leads with White PTFE Insulation. Device is Encapsulated in Stycast Epoxy Resin.

FEATURES

Interchangeability
 Proven Stability and Reliability
 Rapid time response
 PTFE Insulated lead Wires
 Thermally Conductive Epoxy Coating
 Temperature range -40 °C to +125°C


APPLICATIONS

Temperature sensing, control and compensation
 Tight Tolerance Instrumentation
 Assembly into probes for a wide variety of applications
 General Instrumentation applications

PERFORMANCE SPECS

Parameters	Units	Value
Nominal Resistance at +25°C	Ohms	10000
10K3A1iA Resistance tolerance from 0°C to +70°C	°C	± 0.1
10K3A1iB Resistance tolerance from 0°C to +70°C	°C	± 0.2
10K3A1iC Resistance tolerance from 0°C to +70°C	°C	± 0.5
10K3A1iD Resistance tolerance from 0°C to +70°C	°C	± 1.0
Alpha Value at +25°C	%/°C	4.39
Beta Value 25/85	K	3976
Tolerance on Beta Value 25/85	%	± 0.5
Time response in Liquids	Seconds	<1
Dissipation Constant in still air	mW/°C	0.85

MECHANICAL DETAILS



	Dimensions		
	A	B	C
	10 ± 2mm	76 ± 2mm	2.4mm Max
Note 1	30 AWG Solid Silver Plated Copper Leads with White PTFE Insulation		
Note 2	Yellow Stycast 2850ft Epoxy		

RESISTANCE V TEMPERATURE TABLE

Temp. °C	Ohms
----------	------

-40	336098
-39	314553
-38	294524
-37	275897
-36	258563
-35	242427
-34	227398
-33	213394
-32	200339
-31	188163
-30	176803
-29	166198
-28	156294
-27	147042
-26	138393
-25	130306
-24	122741
-23	115661
-22	109032
-21	102824
-20	97006
-19	91553
-18	86439
-17	81641
-16	77138
-15	72911
-14	68940
-13	65209
-12	61703
-11	58405
-10	55304
-9	52385
-8	49638
-7	47050
-6	44613
-5	42317
-4	40151
-3	38110
-2	36184
-1	34366
0	32651

Temp. °C	Ohms
----------	------

1	31031
2	29500
3	28054
4	26687
5	25395
6	24172
7	23016
8	21921
9	20885
10	19903
11	18973
12	18092
13	17257
14	16465
15	15714
16	15001
17	14324
18	13682
19	13073
20	12493
21	11943
22	11420
23	10923
24	10450
25	10000
26	9572
27	9165
28	8777
29	8408
30	8056
31	7721
32	7402
33	7097
34	6807
35	6530
36	6266
37	6014
38	5774
39	5544
40	5325
41	5116

Temp. °C	Ohms
----------	------

42	4916
43	4724
44	4542
45	4367
46	4200
47	4040
48	3887
49	3741
50	3601
51	3467
52	3339
53	3216
54	3098
55	2985
56	2877
57	2773
58	2674
59	2579
60	2487
61	2399
62	2315
63	2234
64	2157
65	2082
66	2011
67	1942
68	1876
69	1813
70	1752
71	1693
72	1637
73	1582
74	1530
75	1480
76	1432
77	1385
78	1341
79	1298
80	1256
81	1216
82	1178

Temp. °C	Ohms
----------	------

83	1141
84	1105
85	1070
86	1037
87	1005
88	974
89	945
90	916
91	888
92	862
93	836
94	811
95	787
96	764
97	741
98	720
99	699
100	678
101	659
102	640
103	622
104	604
105	587
106	571
107	555
108	539
109	524
110	510
111	496
112	482
113	469
114	457
115	444
116	432
117	421
118	410
119	399
120	388
121	378
122	368
123	359
124	350
125	341

ORDERING INFORMATION

Part Number	Description	Ω @25°C	MOQ
10K3A1iA	Series II Thermistor – Epoxy Coated	10000	1,000*
10K3A1iB	Series II Thermistor – Epoxy Coated	10000	1,000*
10K3A1iC	Series II Thermistor – Epoxy Coated	10000	1,000*
10K3A1iD	Series II Thermistor – Epoxy Coated	10000	1,000*

* For quantities less than Minimum Order Quantity – Contact Distribution

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
910 Turnpike Road
Shrewsbury, MA 01545
Tel: 1-508-842-0516
Fax: 1-508-842-0342
Sales:
temperature.cs.amer@meas-spec.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Ballybrit Business Park
Galway Ireland
Tel: +353-91-753238
Fax: +353-91-770789
Sales:
temperature.cs.emea@meas-spec.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
No. 26 Langshan Road
Shenzhen High-Tech Park (North)
Nanshan District, Shenzhen 518057
China
Tel: +86 755 3330 5088
Fax: +86 755 3330 5099
Sales:
temperature.cs.asia@meas-spec.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[GA10K3A1IA](#)