

# SPECIFICATION CONTROL DRAWING


55/0814

TITLE	WIRE, RADIATION-CROSSLINKED, MODIFIED, ETFE INSULATED, NORMAL WEIGHT, OUTER SPACE	Date	07-08-04	Revision	C
-------	---	------	----------	----------	---

This specification sheet forms a part of the latest issue of Raychem Specification 55/.

CONDUCTOR - SILVER-COATED HIGH STRENGTH COPPER ALLOY

INSULATION - RADIATION-CROSSLINKED, MODIFIED ETFE, Primary Insulation shall be of a contrasting pigmentation to that of the jacket



JACKET - LOW OUTGASSING RADIATION-CROSSLINKED, MODIFIED ETFE

TABLE I. CONSTRUCTION DETAILS

PART NUMBER 1/	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	DIAMETER OF STRANDED CONDUCTOR (in.)		FINISHED WIRE		
			MINIMUM	MAXIMUM	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (in.)	MAXIMUM WEIGHT (lbs/1000 ft.)
55/0814-28-*	28	7 x 36	.014	.016	74.4	.035 ± .002	1.3
55/0814-26-*	26	19 x 38	.018	.020	44.8	.040 ± .002	1.7
55/0814-24-*	24	19 x 36	.023	.025	28.4	.045 ± .002	2.3
55/0814-22-*	22	19 x 34	.029	.031	17.5	.050 ± .002	3.3
55/0814-20-*	20	19 x 32	.037	.039	10.7	.058 ± .002	4.8
55/0814-18-*	18	19 x 30	.046	.050	6.8	.070 ± .003	7.5

TABLE II. PERFORMANCE DETAILS

PART NUMBER 1/	BEND TESTING	
	MANDREL DIAMETER (inch) (± 3%)	WEIGHT (lb) (± 3%)
	CROSSLINK VERIFICATION	CROSSLINK VERIFICATION
55/0814-28-*	.375	.250
55/0814-26-*	.375	.500
55/0814-24-*	.500	.750
55/0814-22-*	.500	1.00
55/0814-20-*	.500	1.50
55/0814-18-*	.750	2.00

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

COLOR: White preferred

IDENTIFICATION AND COLOR STRIPING DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

INSULATION ELONGATION: 50% (minimum)

INSULATION FLAWS:

Primary Insulation,

Spark Test, 1.5 kV (rms)

Impulse Dielectric Test, 6.0 kV (peak)

Finished Wire,

Spark Test, 3.0 kV (rms)

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS: .009 in. (minimum) (total insulation)

RADIATION RESISTANCE: 500 megarads

SHRINKAGE: 230 ± 3°C for 1 hour, 0.125 in. (maximum) in 12 in.

VACUUM STABILITY:

Total Mass Loss (TML), 1.0% (maximum)

Volatile Condensable Material, 0.1% (maximum)

VOLTAGE WITHSTAND TEST (Post Environmental):

2500 volts (rms), 60 Hz, 5 minutes

PART NUMBER:

The "\*" in the part numbers above shall be replaced by a color code designator.

1/ Example: AWG 20, white: 55/0814-20-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.



Raychem Wire & Cable  
501 Oakside Avenue  
Redwood City, CA 94063-3800  
Phone: 1-800-227-8816  
Fax: 1-650-361-6297

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[55/0814-22-0](#) [55/0814-28-9](#) [55/0814-26-0](#) [55/0814-22-2](#) [55/0814-24-0](#) [55/0814-24-4](#) [55/0814-24-9](#) [55/0814-28-0](#)  
[55/0814-26-2](#) [55/0814-20-2](#) [55/0814-26-9](#)